

Specifications



Eaton 3031W

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 30A, Flush mount, 120/277V, Back/side, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, 1-pole, 1-pole, Brass, Polycarbonate

General specifications

PRODUCT NAME	Eaton Arrow Hart industrial grade toggle switch
CATALOG NUMBER	3031W
UPC	032664736223
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.005 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	NAFTA
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Industrial grade toggle switch

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	30A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Industrial
WIRING METHOD	Back and side
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
LOAD TYPE	HAL Fan CFL LED MLV FLR ELV INC Motor Control
MATERIAL	Polycarbonate
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	18 lbf-inch
TERMINAL ENCLOSURE MATERIAL	Brass
COLOR	White

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 3031W Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

