



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



303284 STRND GRND Tail #10FORK/#10RING/SCRW, 1, 000/Box

Ideal

Catalog Number	303284
Manufacturer	Ideal
Description	Grounding Tail, Connection: #10 Fork and #10 Ring and Ground Screw, Wire Size: 12 Awg, Green, Wire Type: Stranded, 7-3/4 In Length, Package: 100/Bundle, C/Us UI Listed, Ensures Compliance With Nec Standards, Rohs Compliant, For Device Grounding Applications
Weight per unit	0.0240 (lbs/each)
Product Category	Patch Cords & Jumpers For VDV

Descriptions

Description	STRND GRND TAIL #10FORK/#10RING/SCRW, 1,000/BOX
extra long description	IDEAL 30-3284 8"JMPER W RNG,SCRW &
Features	Coming in various lengths and styles, IDEAL Grounding Pigtailes are designed for a wide variety of grounding applications to help ensure compliance with Article 250 of the National Electric Code. Whether you need solid or stranded, fork or stripped end, small packaging for the occasional use or bulk packaging for the big jobs, we have a solution. The ultra-flexible lead wire and bonding jumpers make for fast and efficient pigtailing and the thread-forming, hole finding ground screw cuts down on installatio
Long Description	Grounding Tail, Connection: #10 Fork And #10 Ring And Ground Screw, Wire Size: 12 AWG, Green, Wire Type: Stranded, 7-3/4 IN Length, Package: 100/Bundle, C/US UL Listed, Ensures Compliance With NEC Standards, RoHS Compliant, For Device Grounding Applications
Product Type	8"Jmper W RNG, SCRW & FRK, 1M BX

Manufacturer Information

Brand	Ideal
GTIN	00783250560967
Manufacturers Part Number	30-3284
UPC	783250560967

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	1000
Weight Per each	0.024