



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



303287 Combo Grounding Tail, 2-Wire Stranded, 25/Bag

Ideal

Catalog Number	303287
Manufacturer	Ideal
Description	Ideal, Grounding Tail, Combo, Wire Size: 12 Awg, Wire Type: Solid, Stranded, Includes: 3-Wire Tail Joined With #10 Ring and Ground Screw, One Stripped Tail and Two #10 Fork Tails
Weight per unit	0.0420 (lbs/each)
Product Category	Patch Cords & Jumpers For VDV

Descriptions

Description	COMBO GROUNDING TAIL, 2-WIRE STRANDED, 25/BAG
extra long description	IDEAL 30-3287 JUMPER W RING,SCRW,FO
Features	Coming in various lengths and styles, IDEAL Grounding Pigtailes are designed for a wide variety of grounding applications to help ensure compliance with Article 250 of the National Electric Code. Whether you need solid or stranded, fork or stripped end, small packaging for the occasional use or bulk packaging for the big jobs, we have a solution. The ultra-flexible lead wire and bonding jumpers make for fast and efficient pigtailing and the thread-forming, hole finding ground screw cuts down on installatio
Long Description	IDEAL, Grounding Tail, Combo, Wire Size: 12 AWG, Wire Type: Solid, Stranded, Includes: 3-Wire Tail Joined With #10 Ring And Ground Screw, One Stripped Tail And Two #10 Fork Tails
Product Type	Jumper W Ring, SCRW, Fork&Strend

Manufacturer Information

Brand	Ideal
GTIN	00783250607921
Manufacturers Part Number	30-3287
UPC	783250607921

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Availability

minimum qty	25
-------------	----

Packaging

Carton	25
Package	100
Weight Per each	0.042