

Specifications



Eaton 3032V

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 30A, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Double-Pole, Dual-pole, Brass, Polycarbonate

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart industrial grade toggle switch |
| CATALOG NUMBER | 3032V |
| UPC | 032664735042 |
| PRODUCT LENGTH/DEPTH | 1.3 in |
| PRODUCT HEIGHT | 4.19 in |
| PRODUCT WIDTH | 1.005 in |
| PRODUCT WEIGHT | 0.001 lb |
| COMPLIANCES | NAFTA |
| CERTIFICATIONS | cULus Listed |
| PRODUCT TYPE | Industrial grade toggle switch |



Powering Business Worldwide

Product specifications

| | |
|------------------------|---------------|
| TYPE | Toggle switch |
| AMPERAGE RATING | 30A |
| VOLTAGE RATING | 120/277 V |
| NUMBER OF POLES | Two-pole |
| APPLICATION | Industrial |
| WIRING METHOD | Back and side |
| SWITCH TYPE | Two-pole |
| MOUNTING METHOD | Flush |
| CONNECTOR TYPE | Screw |

| | |
|------------------|---|
| LOAD TYPE | Fan HAL ELV INC FLR LED CFL MLV Motor Control |
|------------------|---|

| | |
|------------------------------------|---------------|
| MATERIAL | Polycarbonate |
| ALLOWABLE WIRE SIZE | #14-10 AWG |
| TORQUE RATING | 18 lbf-inch |
| TERMINAL ENCLOSURE MATERIAL | Brass |
| COLOR | Ivory |

Resources

| | |
|-------------------------------|---|
| MULTIMEDIA | Arrow Hart - Connecting Safety to Reliability since 1890 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - 3032V Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

