



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30452J Wing-Nut Wire Conn, Model 452 Red, 300/Jar

*Ideal*

Catalog Number	30452J
Manufacturer	Ideal
Description	Twist-On Wingnut, Red Insulation Color, +221 °F Operating Temperature, 1 to 6 Conductors, 600 V Ac, 0.01 LB
Weight per unit	0.0090 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant polypropelene shell
Voltage Rating	600

### Material, Color, and Finish

Color	Red
-------	-----

### Descriptions

Description	WING-NUT WIRE CONN, MODEL 452 RED, 300/JAR
extra long description	IDEAL 30-452J WINGNUT 452 RED, 300
Features	Largest range in the Industry - from 2 #18 to up 4 #10High-leverage, contoured wing provides superior torque on every twistWide range, live-action spring handles small combinations and expands to accommodate large combinations as you need itCopolymer shell expands for smooth, progressive tightening providing dependable connectionsRemovable for repeat usage on same size or larger combinationsMore power with every twist.The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of

### Manufacturer Information

Brand	Ideal
GTIN	00783250216758
UPC	783250216758

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Twist-On

### Availability

minimum qty	300
-------------	-----

### Packaging

Carton	300
Package	1800
Weight Per each	0.009



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E, RoHS Compliant