

## Fish Tape Selection Guide



Length	Width & Thickness	Case Diameter	End Type	Tuff-Grip™ Pro	Tape-Pak® w/footage counter	Rapid-Pak®	Thumb-Winder™	Replacement Tapes
<b>Blued Steel</b>								
25	1/8 in. x .045 in.	7 in.	Formed hook	–	–	–	31-012	–
50	1/8 in. x .045 in.	7 in.	Formed hook	–	–	–	31-010	–
50	1/8 in. x .060 in.	9 in.	Formed hook	31-033**	–	–	–	–
60	1/8 in. x .060 in.	12 in.	Formed hook	31-055	–	–	–	31-035
100	1/8 in. x .060 in.	12 in.	Formed hook	–	31-126	31-081†	–	31-036
120	1/8 in. x .060 in.	12 in.	Formed hook	31-056	–	–	–	31-036
200	1/8 in. x .060 in.	12 in.	Formed hook	–	31-127	31-098†	–	31-038
240	1/8 in. x .060 in.	12 in.	Formed hook	31-057	–	–	–	31-038
500	1/8 in. x .060 in.	None	Formed hook	–	–	–	–	31-3380
700	1/8 in. x .060 in.	None	Formed hook	–	–	–	–	31-3379
50	1/4 in. x .060 in.	12 in.	Formed hook	31-058	–	–	–	31-051
100	1/4 in. x .060 in.	12 in.	Formed hook	31-059	–	–	–	31-050
300	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-2127
400	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-2128
600	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-2980
750	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-2139
1,000	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-3384
10,000	1/4 in. x .060 in.	None	Formed hook	–	–	–	–	31-2982
<b>Stainless Steel</b>								
120	1/8 in. x .060 in.	12 in.	Formed hook	31-066	–	–	–	31-073
240	1/8 in. x .060 in.	12 in.	Formed hook	31-067	–	–	–	31-074
<b>S-Class® Nylon Jacketed Fiberglass</b>								
50	3/16 in. diameter	12 in.	Leader	31-060	–	31-187†	–	31-150
50	3/16 in. diameter	12 in.	Eyelet	31-062	–	31-190†	–	31-160
100	3/16 in. diameter	12 in.	Leader	31-061	–	31-186†	–	31-152
100	3/16 in. diameter	12 in.	Eyelet	31-063	–	31-189†	–	31-162
200	3/16 in. diameter	16 in.	Leader	31-064*	–	31-207†	–	31-155
200	3/16 in. diameter	16 in.	Eyelet	31-065*	–	31-208†	–	31-165
300	3/16 in. diameter	None	Eyelet	–	–	–	–	31-2138
400	3/16 in. diameter	None	Eyelet	–	–	–	–	31-400
500	3/16 in. diameter	None	Eyelet	–	–	–	–	31-3370
<b>Gold-Fish® Brass Plated Steel Coil</b>								
25	3/16 in. diameter	None	Eyelet	–	–	–	–	31-140
50	3/16 in. diameter	12 in.	Eyelet	31-144	–	–	–	31-141
100	3/16 in. diameter	None	Eyelet	–	–	–	–	31-142
<b>Zoom™ Nylon Jacketed Stainless Steel</b>								
50	3/16 in. diameter	12 in.	Eyelet	31-090	–	–	–	31-091
100	3/16 in. diameter	12 in.	Eyelet	31-092	–	–	–	31-093
200	3/16 in. diameter	16 in.	Eyelet	31-096*	–	–	–	31-097

\*16 in. diameter Tuff-Grip™ Case †16 in. diameter Rapid-Pak® Case

\*\*9 in. diameter Tuff-Grip™ Pro Case

Description	Cat. No.
Fish Tape Leader for steel or stainless steel tapes	<b>31-148</b>
Fish Tape Leader for S-Class® Fiberglass	<b>31-159</b>
Multi-Wire Pulling Leader – 6-loop	<b>31-146</b>
Multi-Wire Pulling Leader – 4-loop	<b>31-147</b>

Description	Cat. No.
Fish Tape Swivel Ball	<b>31-085</b>
Replacement Eyelets (4) for S-Class®	<b>31-158</b>
Replacement Eyelets (2) for Zoom™	<b>31-094</b>