



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



329B 3-1/2" Plastic Bushing 150C *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 329B |
| Manufacturer | Bridgeport Fittings |
| Description | Bushing, Plastic - 150 Degrees C, Size 3 1/2 Inch |
| Weight per unit | 0.0960 (lbs/each) |
| Product Category | Plastic |

Features

| | |
|----------|---------|
| Material | Plastic |
| media | Yes |

Material, Color, and Finish

| | |
|--------|-----------|
| Color | Black |
| Finish | NO FINISH |

Dimensions and Weight

| | |
|------|-------|
| Size | 3-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|---|
| Description | 3-1/2" PLASTIC BUSHING 150C |
| extra long description | BPT 329-B 3-1/2" PLASTIC BUSHING 15 |
| Long Description | Bushing, Plastic - 150 Degrees C, Size 3 1/2 Inch |
| Product Type | 3-1/2" Plastic Bushing 150 C |
| Special Features | Black Color, rated 150 degree C. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747403292 |
| Manufacturers Part Number | 329-B |
| UPC | 781747403292 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type | BUSHING |

Trade Size

| | |
|------------|-----|
| Trade Size | 3.5 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.096 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. |
| standard | UL, CSA |
| Temperature Rating | 150° |