

Eaton 32B-BOX

Catalog Number: 32B-BOX

Eaton power device receptacle, Range, #12 - 4 AWG, 50A, Flush, 125/250V, Back, Brown, NEMA 10-50R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Plug, Glass-filled nylon, Power, Used with S80

General specifications



Product Name	Catalog Number
Eaton power device receptacle	32B-BOX
UPC	Product Length/Depth
032664198403	8.5 in
Product Height	Product Width
2.25 in	6 in
Product Weight	Compliances
0.25 lb	NAFTA RoHS Compliant
Certifications	
UL Listed NOM	

Product specifications

Used with

S80

Special features

Range

Amperage Rating

50 A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Three-pole

Color

Brown

Connection type

Plug

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

10-50R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, three-wire, non grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 32B-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)