



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3861 Straight Blade Recept 50A 125/250V

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 3861  |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Power Outlet Angle Plug, 30/50 A, 250 V Ac, 3 Poles, 3 Wires, Black, Nylon Material, 1.36 In Diameter, 3.3 In Length, 0.57 LB |
| Weight per unit  | 0.5650 (lbs/each)   |
| Product Category | Plugs, Connectors, Inlets, Out  |

### Features

|                 |               |
|-----------------|---------------|
| amperage rating | 30/50         |
| connection      | Non Grounding |
| Poles           | 3-way         |
| Voltage         | 250.0 V       |
| Wire Size       | 4             |

### Dimensions and Weight

|      |        |
|------|--------|
| Size | 3.3 in |
|------|--------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | STRAIGHT BLADE RECP 50A 125/250V                    |
| extra long description | P&S 3861 ANG PLUG 30/50AMP 125/250V                 |
| Special Features       | Plastic snap in wire clamp with aluminum conductors |

### Manufacturer Information

|       |                  |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN  | 00785007793901   |
| UPC   | 785007793901     |

### Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | Residential cord connectors |
| Type                 | Power Outlet Angle Plug     |

### Trade Size

|          |      |
|----------|------|
| Amperage | 30.0 |
|----------|------|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 12    |
| Weight Per each | 0.565 |

### Uses, Certifications, and Standards

|          |            |
|----------|------------|
| standard | UL, UL 498 |
|----------|------------|