

Retrofit SNAP²IT[®] MC Cable Connectors

Made in USA 

MORE
on
reverse

No Tools – Saves Time! • For Old Work Installations



Snap connector
on installed
MC cable...

NEW!

SNAP²IT
Connectors
for Retrofit


EASY INSTALLATION IN RETROFIT WORK!



38RAST



40RAST
tinted red inside



Snap
assembly
into box.
Done!

Arlington's new one-piece **RETROFIT SNAP²IT[®]** fittings are *easy to use in an OLD WORK installation* – and handle the widest variety of cables!

They are ideal for adding additional circuits to a load center. And you get the same labor-savings in a retrofit installation!

Installation is quick and easy with **NO TOOLS** required. Install into the knockout in an existing box, pulling the cable/conduit through the KO. Slip the fitting onto the cable, then snap the assembly into the box. That's it!

- **Widest total cable ranges**
Our retrofit Snap²It[®] connectors accommodate cables from 14/2 to 10/3.
- **Widest variety of cables**
For AC, MC, HCF, MC continuous corrugated aluminum cable, MCI-A cables (steel and aluminum), AC90, ACG90 and FLEX.
- **Super-secure installation**
No pullout!
- **Fully assembled one-piece design**




Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com


Retrofit SNAP²IT[®] MC Cable Connectors

Made in USA 


Easy Snap-In Installation • No Tools!




Pull MC cable through knockout in installed old work box.




Snap fitting onto cable.




Push assembly into box...



...snapping it into the box.
Fast and easy. No tools required!



38RAST
with insulated throat



40RAST
with insulated throat and red tint inside

Snap2It[®] Connectors for Retrofit


| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | CABLE TYPE | DIAMETER RANGE | CABLE RANGE | UNIT PKG | STD PKG |
|---------------------------------|---------------------------|--|----------------|------------------------------------|----------|---------|
| 38RAST with insulated throat | 13586 | MC/HCF/AC Steel & Aluminum | .405 to .605 | 14/2 and 12/2 w/ and w/o ground | ----- | ----- |
| | | MCI-A Steel & Aluminum | .440 to .550 | 14/3, 14/4, | | |
| | | AC90, ACG90 | .440 to .550 | 12/3, 12/4, | 25 | 25 |
| | | Flexible Metal Conduit Steel & Aluminum (RWFMC) | 3/8" Flex* | 10/2, 10/3 | ----- | ----- |

*CSA Listed w/ anti-short bushing ONLY

Tinted red inside fitting

| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | CABLE TYPE | DIAMETER RANGE | CABLE RANGE | UNIT PKG | STD PKG |
|---------------------------------|---------------------------|--|----------------|--|----------|---------|
| 40RAST with insulated throat | 13587 | MC/HCF/AC Steel & Aluminum | .485 to .610 | 14/3, 12/2 and 12/3 w/ and w/o ground | ----- | ----- |
| | | MCI-A Steel & Aluminum | .480 to .580 | 14/4, | | |
| | | AC90, ACG90 | .480 to .550 | 12/4, | 25 | 25 |
| | | Flexible Metal Conduit Steel & Aluminum (RWFMC) | 3/8" Flex* | 10/2, 10/3 | ----- | ----- |

*CSA Listed w/ anti-short bushing ONLY



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Patent pending

Distributed by

Retrofit SNAP²IT[®] MC Cable Connectors

Made in USA 

MORE
on
reverse

No Tools – Saves Time! • For Old Work Installations



Snap connector
on installed
MC cable...

NEW!

**SNAP²IT
Connectors
for Retrofit**


EASY INSTALLATION IN RETROFIT WORK!



38RAST



40RAST
tinted red inside



Snap
assembly
into box.
Done!

Arlington's new one-piece **RETROFIT SNAP²IT[®]** fittings are *easy to use in an OLD WORK installation* – and handle the widest variety of cables!

They are ideal for adding additional circuits to a load center. And you get the same labor-savings in a retrofit installation!

Installation is quick and easy with **NO TOOLS** required. Install into the knockout in an existing box, pulling the cable/conduit through the KO. Slip the fitting onto the cable, then snap the assembly into the box. That's it!

- **Widest total cable ranges**
Our retrofit Snap²It[®] connectors accommodate cables from 14/2 to 10/3.
- **Widest variety of cables**
For AC, MC, HCF, MC continuous corrugated aluminum cable, MCI-A cables (steel and aluminum), AC90, ACG90 and FLEX.
- **Super-secure installation**
No pullout!
- **Fully assembled one-piece design**


 
Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com


Retrofit SNAP²IT[®] MC Cable Connectors

Made in USA 


Easy Snap-In Installation • No Tools!




Pull MC cable through knockout in installed old work box.




Snap fitting onto cable.




Push assembly into box...



...snapping it into the box.
Fast and easy. No tools required!



38RAST
with insulated throat



40RAST
with insulated throat and **red tint** inside

Snap2It[®] Connectors for Retrofit


| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | CABLE TYPE | DIAMETER RANGE | CABLE RANGE | UNIT PKG | STD PKG |
|--|---------------------------|---|----------------|------------------------------------|----------|---------|
| 38RAST with insulated throat | 13586 | MC/HCF/AC Steel & Aluminum | .405 to .605 | 14/2 and 12/2 w/ and w/o ground | ----- | ----- |
| | | MCI-A Steel & Aluminum | .440 to .550 | 14/3, 14/4, | | |
| | | AC90, ACG90 | .440 to .550 | 12/3, 12/4, | 25 | 25 |
| | | Flexible Metal Conduit Steel & Aluminum (RWFMC) | 3/8" Flex* | 10/2, 10/3 | ----- | ----- |

*CSA Listed w/ anti-short bushing ONLY

Tinted red inside fitting

| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | CABLE TYPE | DIAMETER RANGE | CABLE RANGE | UNIT PKG | STD PKG |
|--|---------------------------|---|----------------|--|----------|---------|
| 40RAST with insulated throat | 13587 | MC/HCF/AC Steel & Aluminum | .485 to .610 | 14/3, 12/2 and 12/3 w/ and w/o ground | ----- | ----- |
| | | MCI-A Steel & Aluminum | .480 to .580 | 14/4, | | |
| | | AC90, ACG90 | .480 to .550 | 12/4, | 25 | 25 |
| | | Flexible Metal Conduit Steel & Aluminum (RWFMC) | 3/8" Flex* | 10/2, 10/3 | ----- | ----- |

*CSA Listed w/ anti-short bushing ONLY



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Patent pending

Distributed by