



TAPE & BARRICADE TAPE

DUCT TAPE

PC 5380



Duct Tape will adhere to all types of surfaces. The polyethylene coated cloth construction provides superior mechanical strength and conforms well to irregular surfaces. It is excellent for bundling, patching and sealing. It tears straight and is curl resistant.

FEATURES:

- 2" x 60 Yards
- Temperature Rating 200° F
- 9 Mil - Cloth Backing
- Individual Cello Wrap
- Colors Available Upon Request

CAT. NO.	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD
DT260	28100	2" x 60 yds	Silver	12	24	19.50#
DT260Red	81064	2" x 60 yds	Red	12	24	19.50#

PIPE WRAP-PVC

PC 5420



Pipe Wrap is a polyvinyl chloride film coated with a rubber resin adhesive which protects pipe, joints, conduit and couplings for overhead or direct burial applications. It is corrosion and puncture resistant.

FEATURES:


- 1", 2" & 4" Widths
- UPC Approved
- 10 Mil and 20 Mil
- Abrasion Resistant
- Provides Electrical Protection
- A Low Lead Product
- Surface Marked



CAT. NO.	UPC	DIMENSIONS	MIL	STD	MSTR	WT/STD
110	28110	1" x 100'	10 Mil	48		29.28#
210	28140	2" x 100'	10 Mil	24		28.80#
410	28142	4" x 100'	10 Mil	12		27.60#
220	28145	2" x 100'	20 Mil	24		53.52#

MASKING TAPE

PC 5410



Masking Tape is a general purpose tape which is tan in color and is supplied for indoor applications. The outdoor version, 200MTBlue, is blue in color and UV resistant. It has a low tack and is easily removed where application and cleanup are several days apart.

FEATURES:

- 2"
- 60 Yard Rolls
- Tan & Blue
- Blue is UV Resistant

MASKING TAPE

CAT. NO.	UPC	DIMENSIONS	STD	MSTR	WT/STD
200MT	30020	2" x 60 yds	24		15.12#

OUTDOOR MASKING TAPE (BLUE)

200MTBlue	28143	2" x 60 yds	24		16.68#
-----------	-------	-------------	----	--	--------

BARRICADE TAPE

PC 5320



Barricade Tape is used for marking physical hazards or off limit areas. Other legends & colors on request. Meets OSHA 1910.144 for marking physical hazards.

3" x 1,000 Ft.

CAT. NO.	UPC	LEGEND	COLOR	STD	MSTR	WT/STD
BT5	16330	Caution Caution Caution	Yellow	1	12	4.86#
BT8	16332	Caution Do Not Enter	Yellow	1	12	4.86#
BT12	16335	Caution High Voltage	Yellow	1	12	4.86#
BT13	16334	Caution Keep Out	Yellow	1	12	4.86#
BT19	16336	Caution Open Trench	Yellow	1	12	4.86#
BT31	16338	Alternating Stripes	Black/Yellow	1	12	4.86#
BT32	16339	Alternating Stripes	Red/White	1	12	4.86#
BT49	16387	Danger Keep Out	Red	1	12	4.86#

3" x 300 Ft.

BT5X3	16331	Caution Caution Caution	Yellow	1	12	1.36#
BT8X3	16333	Caution Do Not Enter	Yellow	1	12	1.36#
BT13X3	16337	Caution Keep Out	Yellow	1	12	1.36#

FEATURES:

- Reusable Polyethylene
- Continuous Warning
- 3" Wide x 1,000 or 300 Ft.
- Custom Legends Available