

# ETP™ 4000S Series Steel EMT Set Screw Connectors

NEC/CEC:  
Listed for Ordinary Locations

## Application

- To ground and secure EMT raceways to boxes and enclosures.

## Features


- Heavy steel walls.
- Concretetight when taped.
- Pre-set/pre-staked set screws.
- Male hub threads — NPS.
- Available with insulated throat.
- Three-way combination screws 1/2" thru 2".
- Slotted hexhead screw 2-1/2" thru 4".
- Insulated throat connector rated +90 °C (+194 °F).
- 2-1/2" thru 4" rated for threadless Aluminum RMC and steel IMC.

## Materials/Finish

- Steel/zinc plated

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E-14895
- CSA Certified: 028507
- NEMA: FB-1



4050S-4100S



4125S - 4400S

### Dimensions in Millimeters (Inches)

Trade Size (Inches)	Body Length	Maximum Diameter	Thread Length	Weight per 100 kg (lb)	Catalog Number	Insulated Throat Catalog Number
1/2	26.2 (1.03)	21.3 (0.84)	11.2 (0.44)	4.54 (10.00)	4050S	4050ST
3/4	27.7 (1.09)	27.4 (1.08)	11.2 (0.44)	6.80 (15.00)	4075S	4075ST
1	30.2 (1.19)	33.3 (1.31)	11.2 (0.44)	10.43 (23.00)	4100S	4100ST
1-1/4	44.5 (1.75)	42.9 (1.69)	14.2 (0.56)	19.05 (42.00)	4125S	4125ST
1-1/2	49.3 (1.94)	49.3 (1.94)	14.2 (0.56)	24.04 (53.00)	4150S	4150ST
2	55.6 (2.19)	60.5 (2.38)	16.0 (0.63)	34.02 (75.00)	4200S	4200ST
2 - 1/2	60.5 (2.38)	79.5 (3.13)	22.4 (0.88)	58.97 (130.00)	4250S	4250ST
3	73.2 (2.88)	95.3 (3.75)	22.4 (0.88)	104.33(230.00)	4300S	4300ST
3 - 1/2	76.2 (3.00)	108.0 (4.25)	25.4 (1.00)	113.40 (250.00)	4350S	4350ST
4	81.0 (3.19)	120.7 (4.75)	25.4 (1.00)	113.40 (250.00)	4400S	4400ST

# ETP™ 4000S Series Steel EMT Set Screw Connectors

NEC/CEC:  
Listed for Ordinary Locations

## Application

- To ground and secure EMT raceways to boxes and enclosures.

## Features

- Heavy steel walls.
- Concretetight when taped.
- Pre-set/pre-staked set screws.
- Male hub threads — NPS.
- Available with insulated throat.
- Three-way combination screws 1/2" thru 2".
- Slotted hexhead screw 2-1/2" thru 4".
- Insulated throat connector rated +90 °C (+194 °F).
- 2-1/2" thru 4" rated for threadless Aluminum RMC and steel IMC.

## Materials/Finish

- Steel/zinc plated

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-14895
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E-14895
- CSA Certified: 028507
- NEMA: FB-1



4050S-4100S



4125S - 4400S

Dimensions in Millimeters (Inches)

Trade Size (Inches)	Body Length	Maximum Diameter	Thread Length	Weight per 100 kg (lb)	Catalog Number	Insulated Throat Catalog Number
1/2	26.2 (1.03)	21.3 (0.84)	11.2 (0.44)	4.54 (10.00)	4050S	4050ST
3/4	27.7 (1.09)	27.4 (1.08)	11.2 (0.44)	6.80 (15.00)	4075S	4075ST
1	30.2 (1.19)	33.3 (1.31)	11.2 (0.44)	10.43 (23.00)	4100S	4100ST
1-1/4	44.5 (1.75)	42.9 (1.69)	14.2 (0.56)	19.05 (42.00)	4125S	4125ST
1-1/2	49.3 (1.94)	49.3 (1.94)	14.2 (0.56)	24.04 (53.00)	4150S	4150ST
2	55.6 (2.19)	60.5 (2.38)	16.0 (0.63)	34.02 (75.00)	4200S	4200ST
2 - 1/2	60.5 (2.38)	79.5 (3.13)	22.4 (0.88)	58.97 (130.00)	4250S	4250ST
3	73.2 (2.88)	95.3 (3.75)	22.4 (0.88)	104.33(230.00)	4300S	4300ST
3 - 1/2	76.2 (3.00)	108.0 (4.25)	25.4 (1.00)	113.40 (250.00)	4350S	4350ST
4	81.0 (3.19)	120.7 (4.75)	25.4 (1.00)	113.40 (250.00)	4400S	4400ST