

# Temporary Lighting Device

43308



Medium base, phenolic, pin type hook supplied, for temporary use. Black.

## features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

## specifications

**General Info**

Type: Incandescent Temporary Lighting Device, Medium Base Lampholder

**Listing Agencies/Third Party Information**

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPS C: 39111803  
UR: No

**Dimensions**

Height U S: 2.0"  
Length U S: 1.44"

**Technical Information**

Volts: 250V  
Volts A C: 250  
Watts: 660

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: Trade Agreement Act Compliant