



Catalog Number: 4460-GHC1-NK  
Item Description: N1 HINGE CVR GUTTER NK  
UPC Code: 784572106635


Brand Name: Milbank  
Type: Lay In Wireway  
Application: Wireway  
Standard: UL Listed, Type 1  
Cover Type: Hinge Cover  
Enclosure: Indoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 60  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False





*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
4460-GHC1(-)	1002943
RC-4460-GHC1(-)	1125051
SPH-445	1132575

NO.	QTY.	PART NO.	DESCRIPTION
1	1	(SEE CHART)	BACK
2	1	(SEE CHART)	TOP
3	5	1003198	HINGE
4	7	1001290	SCREW, 10-32 X 5/16
5	1	(SEE CHART)	LABEL (U/L LISTING)
6	1	1002900	LABEL, WIREWAY FITTING
7	3	1002880	BAG ASSY.



SUFFIX	BACK #	COVER #
-SU	1105200	1002281
-SUC	1128809	1118926
-SO	1128810	1128772
-SUNK	1110151	1002281
-NK	1128811	1128772
-SUNKC	1128812	1118926



SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED

NOTE:  
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

Material:	16 GA. - SEE CHART	General Offices: Kansas City, MO
Shear/ Die#:		
Finish:	SEE CHART	Title: HINGE COVER WIREWAY 4 x 4 x 60, TYPE 1 NEMA ENCLOSURE
Part Wt.:		Catalog No.: (SEE CHART)
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*		Customer: MILBANK STANDARD
Third Angle 		Drawing No.: 355-11
Scale:	NTS	Date: 05/09/02
Drawn By:	DY	Sheet 1 of 1
Checked By:		
Approved By:		

REV	DATE	DESCRIPTION	BY	DL
D	8-27-07	ADDED BACK & COVER CHART & IT. 1001290 QTY. W 10 ECO. 15946		
D1	4/9/08	ADDED CHART & REMOVED NOTE #2 (ECO.17139)	JLT	



Catalog Number: 4460-GHC1-NK  
Item Description: N1 HINGE CVR GUTTER NK  
UPC Code: 784572106635


Brand Name: Milbank  
Type: Lay In Wireway  
Application: Wireway  
Standard: UL Listed, Type 1  
Cover Type: Hinge Cover  
Enclosure: Indoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 60  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False





*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
4460-GHC1(-)	1002943
RC-4460-GHC1(-)	1125051
SPH-445	1132575

NO.	QTY.	PART NO.	DESCRIPTION
1	1	(SEE CHART)	BACK
2	1	(SEE CHART)	TOP
3	5	1003198	HINGE
4	7	1001290	SCREW, 10-32 X 5/16
5	1	(SEE CHART)	LABEL (U/L LISTING)
6	1	1002900	LABEL, WIREWAY FITTING
7	3	1002880	BAG ASSY.



SUFFIX	BACK #	COVER #
-SU	1105200	1002281
-SUC	1128809	1118926
-SO	1128810	1128772
-SUNK	1110151	1002281
-NK	1128811	1128772
-SUNKC	1128812	1118926



SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED

NOTE:  
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

Material:	16 GA. - SEE CHART	General Offices: Kansas City, MO
Shear/ Die#:		
Finish:	SEE CHART	Title: HINGE COVER WIREWAY 4 x 4 x 60, TYPE 1 NEMA ENCLOSURE
Part Wt.:		Catalog No.: (SEE CHART)
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2"		Customer: MILBANK STANDARD
Third Angle 		Drawing No.: 355-11
Scale:	NTS	Date: 05/09/02
Drawn By:	DY	Sheet 1 of 1
Checked By:		
Approved By:		

REV	DATE	DESCRIPTION	BY	DL
D	8-27-07	ADDED BACK & COVER CHART & IT. 1001290 QTY. W 10 ECO. 15946		
D1	4/9/08	ADDED CHART & REMOVED NOTE #2 (ECO.17139)	JLT	