



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



45092 Stripmaster Wire Stripper, 10-22 Awg

Ideal

| | |
|------------------|--|
| Catalog Number | 45092 |
| Manufacturer | Ideal |
| Description | Stripmaster Standard Wire Stripper, Size: 10 - 22 Awg, Cushion Grip Handle, Die-Cast Frame, Die-Cast Handle, Knife-Type Blade, Stripping Range: Up to 7/8 In, Strip Hole Size: 0.144 In For 10 Awg, 0.113 In For 12 Awg, 0.09 In For 14 Awg, 0.072 For 16 Awg, 0.061 For 18 Awg, 0.048 For 20 Awg, 0.048 For 22 Awg, For PVC Vinyl Insulations |
| Weight per unit | 0.9000 (lbs/each) |
| Product Category | Strippers |

Features

| | |
|-------------|----------------|
| Handle Type | CUSHION GRIP |
| Material | Die-Cast Frame |

Material, Color, and Finish

| | |
|-----------------|----------|
| Handle Material | Die-Cast |
|-----------------|----------|

Dimensions and Weight

| | |
|------|---------|
| Size | 10 - 22 |
|------|---------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | STRIPMASTER WIRE STRIPPER, 10-22 AWG |
| extra long description | IDEAL 45-092 STM STD 10-22GA |
| Features | The versatile Stripmaster/Stripmaster Lite Wire Strippers are the standard of the industry. They incorporate a gripper that firmly holds the wire in a center-line position with the stripping hole. The lever action of the stripper offers a mechanical advantage that makes stripping easier. This aids in production applications and reduces operator fatigue. One squeeze strips the wire clean, up to a full 7/8 in. (22mm). The jaws are automatically held open to allow removal of the wire without damaging its end. This s |
| Long Description | Stripmaster Standard Wire Stripper, Size: 10 - 22 AWG, Cushion Grip Handle, Die-Cast Frame, Die-Cast Handle, Knife-Type Blade, Stripping Range: Up To 7/8 IN, Strip Hole Size: 0.144 IN For 10 AWG, 0.113 IN For 12 AWG, 0.09 IN For 14 AWG, 0.072 For 16 AWG, 0.061 For 18 AWG, 0.048 For 20 AWG, 0.048 For 22 AWG, For PVC Vinyl Insulations |
| Product Type | STM STD 10-22ga |
| Special Features | Cleanly strips wire up to 7/8 IN (22 MM); Eliminates nicking, cutting and fraying of wire; Knife-type blades; One-third less hand pressure for each strip; Precision-ground, knife-type blades provide clean, accurate stripping; Spring-action motion increases leverage and reduces operator fatigue; Sturdy die-cast frame provides long-term durability; Wire gripper holds wire centered in hole |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250450923 |
| Manufacturers Part Number | 45-092 |
| UPC | 783250450923 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | HAND TOOLS |
| Type | Standard Wire Stripper |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.9 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | For PVC Vinyl Insulations |
|-------------|---------------------------|