
46558

F32T8 ADV850/ALTO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 36000

Base: Medium Bi-Pin (G13)

Bulb: T8

Coating: Copolymer

Color: ADV850

Color Temperature: 5000K

CRI: 82

Diameter: 1.00 IN

Initial Lumens: 3100

Lamp Type: Fluorescent

Length: 48.00 IN

Mean Design Lumens: 3025

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Package Weight: 15.40 L

Pack By: 30

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585465583

Wattage: 32.0 W

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone

46558

F32T8 ADV850/ALTO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 36000

Base: Medium Bi-Pin (G13)

Bulb: T8

Coating: Copolymer

Color: ADV850

Color Temperature: 5000K

CRI: 82

Diameter: 1.00 IN

Initial Lumens: 3100

Lamp Type: Fluorescent

Length: 48.00 IN

Mean Design Lumens: 3025

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Package Weight: 15.40 L

Pack By: 30

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585465583

Wattage: 32.0 W

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone