



# M18 REDLITHIUM™

## THE WORLD'S FIRST & ONLY 18V HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



## 9" 5 TPI The Ax™ Sawzall® Blade (5 Pk)

48-00-5026

### Where to Buy

- Shop Online
- Find Local



### Features

- **NAIL GUARD™.** Ordinary teeth deliver either speed or durability. NAIL GUARD™ solves this trade-off with an aggressive 5 TPI pattern for faster cuts and a unique design that protects against tooth fracture.
- **FANG TIP™.** Ordinary tips bounce or skate on the work piece. FANG TIP™ bites into the wood on first contact.
- A thicker, more rigid blade body resists fracturing and bending for maximum durability.
- The 1" tall blade body reduces blade twisting for straighter, more accurate cuts.
- Matrix II bi-metal teeth for greater durability.

### Overview

The Ax Sawzall® blades have been engineered to deliver the fastest cuts, longest life, greatest tooth durability and quickest plunge cuts of any wood demolition blade on the market.

### Model Options

### Specifications

<b>TPI</b>	5
<b>Length</b>	9.09"
<b>Profile</b>	Demo
<b>Pack Qty</b>	5 Pack
<b>Shank</b>	1/2" Universal
<b>Material</b>	Wood with Nails

Item/Cat #	TPI	Length	Profile	Pack Qty
------------	-----	--------	---------	----------

48-00-5021	5	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-5026	5	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5027	5	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-8021	5	6.06"	Demo	25 Pack	Shop Online Find Local
48-00-8026	5	9.09"	Demo	25 Pack	Shop Online Find Local
48-00-8027	5	95.12"	Demo	25 Pack	Shop Online Find Local
48-01-2001	5	6.06"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2006	5	9.09"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2007	5	95.12"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2021	5	6.06"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2026	5	9.09"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2027	5	95.12"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-7021	5	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7026	5	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7027	5	95.12"	Demo	100 Pack (Bulk)	Shop Online Find Local



# M18 REDLITHIUM™

## THE WORLD'S FIRST & ONLY 18V HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



### 9" 5 TPI The Ax™ Sawzall® Blade (5 Pk)

48-00-5026

#### Where to Buy

- Shop Online
- Find Local



#### Features

- **NAIL GUARD™**. Ordinary teeth deliver either speed or durability. NAIL GUARD™ solves this trade-off with an aggressive 5 TPI pattern for faster cuts and a unique design that protects against tooth fracture.
- **FANG TIP™**. Ordinary tips bounce or skate on the work piece. FANG TIP™ bites into the wood on first contact.
- A thicker, more rigid blade body resists fracturing and bending for maximum durability.
- The 1" tall blade body reduces blade twisting for straighter, more accurate cuts.
- Matrix II bi-metal teeth for greater durability.

#### Specifications

<b>TPI</b>	5
<b>Length</b>	9.09"
<b>Profile</b>	Demo
<b>Pack Qty</b>	5 Pack
<b>Shank</b>	1/2" Universal
<b>Material</b>	Wood with Nails

#### Overview

The Ax Sawzall® blades have been engineered to deliver the fastest cuts, longest life, greatest tooth durability and quickest plunge cuts of any wood demolition blade on the market.

#### Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty
------------	-----	--------	---------	----------

48-00-5021	5	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-5026	5	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5027	5	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-8021	5	6.06"	Demo	25 Pack	Shop Online Find Local
48-00-8026	5	9.09"	Demo	25 Pack	Shop Online Find Local
48-00-8027	5	95.12"	Demo	25 Pack	Shop Online Find Local
48-01-2001	5	6.06"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2006	5	9.09"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2007	5	95.12"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2021	5	6.06"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2026	5	9.09"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2027	5	95.12"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-7021	5	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7026	5	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7027	5	95.12"	Demo	100 Pack (Bulk)	Shop Online Find Local