



M18 REDLITHIUM™

THE WORLD'S FIRST & ONLY 18V HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



9" 14 TPI The Torch™ SAWZALL® Blades (5 Pk)

48-00-5787



Where to Buy

- Shop Online
- Find Local

Features

- Optimized tooth design providing 2X more life than our previous generation
- SAWZALL® blades Tough Neck™ ribs strengthen the blade tang and minimize breakage
- Grid Iron™ honeycomb pattern increases blade rigidity to resist blade buckling

Specifications

TPI	14
Length	9.09"
Profile	Demo
Pack Qty	5 Pack
Shank	1/2" Universal
Material	Scheduled 80 Pipe Angle Iron

Overview

The Torch™ metal-cutting blades with the Double Duty Upgrade™ feature a tooth form optimized for the longest life and maximum durability. Tough Neck™ is engineered to protect against tang breakage and delivers the strongest SAWZALL® blade tang on the market. Grid Iron™ features a stamped honeycomb pattern throughout the body of the blade that greatly increases the rigidity of the blade, making it the stiffest metal cutting SAWZALL® blade on the market. These blades are ideal for making tough, straight cuts.

Model Options

Item/Cat #	TPI	Length	Profile	Pack Qty	
48-00-5712	10	6.06"	Demo	5 Pack	Shop Online Find Local

Item/Cat #	TPI	Length	Profile	Pack Qty	
48-00-5713	10	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5714	10	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-5782	14	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-5784	18	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-5786	24	6.06"	Demo	5 Pack	Shop Online Find Local
48-00-5787	14	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5788	18	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5789	18	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-5790	24	9.09"	Demo	5 Pack	Shop Online Find Local
48-00-5791	24	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-5794	14	95.12"	Demo	5 Pack	Shop Online Find Local
48-00-8712	10	6.06"	Demo	25 Pack	Shop Online Find Local
48-00-8713	10	9.09"	Demo	25 Pack	Shop Online Find Local
48-00-8782	14	6.06"	Demo	25 Pack	Shop Online Find Local
48-00-8784	18	6.06"	Demo	25 Pack	Shop Online Find Local
48-00-8787	14	9.09"	Demo	25 Pack	Shop Online Find Local
48-00-8788	18	9.09"	Demo	25 Pack	Shop Online Find Local

Item/Cat #	TPI	Length	Profile	Pack Qty	
48-00-8789	18	95.12"	Demo	25 Pack	Shop Online Find Local
48-01-2703	10	9.09"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2712	10	6.06"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2713	10	9.09"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2714	10	95.12"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2762	14	6.06"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2764	18	6.06"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2767	14	9.09"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2768	18	9.09"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2769	18	95.12"	Demo	10 Pack (Bulk)	Shop Online Find Local
48-01-2782	14	6.06"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2784	18	6.06"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2787	14	9.09"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2788	18	9.09"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2789	18	95.12"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-2794	14	95.12"	Demo	25 Pack (Bulk)	Shop Online Find Local
48-01-7712	10	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7713	10	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local

Item/Cat #	TPI	Length	Profile	Pack Qty	
48-01-7782	14	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7784	18	6.06"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7787	14	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7788	18	9.09"	Demo	100 Pack (Bulk)	Shop Online Find Local
48-01-7789	18	95.12"	Demo	100 Pack (Bulk)	Shop Online Find Local