



ITEM# 49-12-KITA



## EXACT™ #6 – 750 MCM Aluminum 12T U Style Die Kit

The M18™ FORCE LOGIC™ 750 MCM Crimper is the Easiest Way to Crimp, producing cULus classified crimps according to the UL 486A-B classification standards for #8 - 750 MCM Cu and Dual Rated Anderson, Blackburn® Burndy, IlSCO, Panduit, Penn-Union and Thomas & Betts Connectors. Milwaukee® EXACT™ 12T U-Style Dies are individually engineered both for quality crimps and for faster connections on all sizes with die lengths specific to each connector. In addition every EXACT™ 12T U-Style Die features vivid industry standard colors to indicate wire size and center alignment markings for easiest die selection and die alignment. All dies also eliminate cross referencing by imprinting the wire size onto completed connectors and are the only dies that are 100% serialized and measured for greatest accuracy and easiest inspection.

## INCLUDES:

[\(1\) 750 MCM Aluminum 12T U-Style Die \(49-12-U750\)](#)  
[\(1\) 600 MCM Aluminum 12T U-Style Die \(49-12-U600\)](#)  
[\(1\) 500 MCM Aluminum 12T U-Style Die \(49-12-U500\)](#)  
[\(1\) 400 MCM Aluminum 12T U-Style Die \(49-12-U400\)](#)  
[\(1\) 350 MCM Aluminum 12T U-Style Die \(49-12-U350\)](#)  
[\(1\) 300 MCM Aluminum 12T U-Style Die \(49-12-U300\)](#)  
[\(1\) 250 MCM Aluminum 12T U-Style Die \(49-12-U250\)](#)  
(1) Carrying Case

[\(1\) 4/0 Aluminum 12T U-Style Die \(49-12-U04A\)](#)  
[\(1\) 3/0 Aluminum 12T U-Style Die \(49-12-U03A\)](#)  
[\(1\) 2/0 Aluminum 12T U-Style Die \(49-12-U02A\)](#)  
[\(1\) 1/0 Aluminum 12T U-Style Die \(49-12-U01A\)](#)  
[\(1\) #1 Aluminum 12T U-Style Die \(49-12-U001\)](#)  
[\(1\) #2 Aluminum 12T U-Style Die \(49-12-U002\)](#)  
[\(1\) #4 Aluminum 12T U-Style Die \(49-12-U004\)](#)  
[\(1\) #6 Aluminum 12T U-Style Die \(49-12-U006\)](#)

## FEATURES:

- 100% Inspected for Critical Dimensions & Serialized to Ensure Crimp Quality
- Die Lengths Specific to Connector Size for Faster Connections on All Sizes
- Wire Size Marked on Each Die for Easy Identification
- Vivid Color Coding & Center Mark for Easiest Selection and Die Alignment
- Die Size Pressed into Connector matches wire size Eliminating Cross Referencing
- Stainless Steel Finish Protects Against Corrosion

## PRODUCT SPECIFICATIONS:

Warranty

No Warranty



ITEM# 49-12-KITA



## EXACT™ #6 – 750 MCM Aluminum 12T U Style Die Kit

The M18™ FORCE LOGIC™ 750 MCM Crimper is the Easiest Way to Crimp, producing cULus classified crimps according to the UL 486A-B classification standards for #8 - 750 MCM Cu and Dual Rated Anderson, Blackburn® Burndy, IlSCO, Panduit, Penn-Union and Thomas & Betts Connectors. Milwaukee® EXACT™ 12T U-Style Dies are individually engineered both for quality crimps and for faster connections on all sizes with die lengths specific to each connector. In addition every EXACT™ 12T U-Style Die features vivid industry standard colors to indicate wire size and center alignment markings for easiest die selection and die alignment. All dies also eliminate cross referencing by imprinting the wire size onto completed connectors and are the only dies that are 100% serialized and measured for greatest accuracy and easiest inspection.

## INCLUDES:

- [\(1\) 750 MCM Aluminum 12T U-Style Die \(49-12-U750\)](#)
- [\(1\) 600 MCM Aluminum 12T U-Style Die \(49-12-U600\)](#)
- [\(1\) 500 MCM Aluminum 12T U-Style Die \(49-12-U500\)](#)
- [\(1\) 400 MCM Aluminum 12T U-Style Die \(49-12-U400\)](#)
- [\(1\) 350 MCM Aluminum 12T U-Style Die \(49-12-U350\)](#)
- [\(1\) 300 MCM Aluminum 12T U-Style Die \(49-12-U300\)](#)
- [\(1\) 250 MCM Aluminum 12T U-Style Die \(49-12-U250\)](#)
- (1) Carrying Case

- [\(1\) 4/0 Aluminum 12T U-Style Die \(49-12-U04A\)](#)
- [\(1\) 3/0 Aluminum 12T U-Style Die \(49-12-U03A\)](#)
- [\(1\) 2/0 Aluminum 12T U-Style Die \(49-12-U02A\)](#)
- [\(1\) 1/0 Aluminum 12T U-Style Die \(49-12-U01A\)](#)
- [\(1\) #1 Aluminum 12T U-Style Die \(49-12-U001\)](#)
- [\(1\) #2 Aluminum 12T U-Style Die \(49-12-U002\)](#)
- [\(1\) #4 Aluminum 12T U-Style Die \(49-12-U004\)](#)
- [\(1\) #6 Aluminum 12T U-Style Die \(49-12-U006\)](#)

## FEATURES:

- 100% Inspected for Critical Dimensions & Serialized to Ensure Crimp Quality
- Die Lengths Specific to Connector Size for Faster Connections on All Sizes
- Wire Size Marked on Each Die for Easy Identification
- Vivid Color Coding & Center Mark for Easiest Selection and Die Alignment
- Die Size Pressed into Connector matches wire size Eliminating Cross Referencing
- Stainless Steel Finish Protects Against Corrosion

## PRODUCT SPECIFICATIONS:

Warranty

No Warranty