


4" OCTAGONAL CONCRETE BOXES

NOTE


- ▶ For Fixture/Luminaire Support of 50 lbs or less
- ▶*For Fixture/Luminaire Support of 90 lbs or less, Fan Support of 70 lbs or less

See Page A5 for Covers & Rings


Cat. No.	Depth	Knockouts		Cu. Inch	Std. Pkg.
		Sides 1, 3, 5, 7	Sides 2, 4, 6, 8		
2CB	2"	1 - 1/2"	1 - 3/4"	24.4	25
25CB	2-1/2"	1 - 1/2"	1 - 3/4"	30.5	25
3CB	3"	1 - 1/2"	1 - 3/4"	37.0	25
3CB-75/100	3"	1 - 3/4"	1 - 1"	37.0	25
35CB	3-1/2"	2 - 1/2"	2 - 3/4"	43.0	25
35CB-75/100	3-1/2"	1 - 3/4"	1 - 1"	43.0	25
4CB	4"	2 - 1/2"	2 - 3/4"	49.2	25
4CB-75/100	4"	2 - 3/4"	2 - 1"	49.2	25
*4CB-F	4"	Side 1, 5; 1 - 1/2" Side 3, 7; 2 - 1/2"	Side 2, 6; 1 - 3/4" Side 4, 8; 2 - 3/4"	49.2	25
5CB	5"	2 - 1/2"	2 - 3/4"	61.7	10
6CB	6"	2 - 1/2"	2 - 3/4"	73.5	10




2CB
25CB
3CB




35CB
4CB
5CB
6CB



3CB-75/100
35CB-75/100




4CB-75/100



FAN-RATED CONCRETE BOX


Inside tabs for fans up to 70 lbs (dynamic)




*4CB-F

4" OCTAGONAL CONCRETE BOX COVERS


Cat. No.	Description	Std. Pkg.
CB-B	Flat, Blank	25
CB-B-PT	Flat, Blank - With 12" #12AWG Solid Pigtail	25
CB-BK	Flat With 3 - 1/2" KO's & 2 - 3/4" KO's	25
CB-BK-STUD	2 - 1/2" KO's & 2 - 3/4" KO's - With #3/8-18 Threaded Fixture Stud	25



CB-B



CB-B-PT



CB-BK



CB-BK-STUD


4" OCTAGONAL CONCRETE BOXES

NOTE


- ▶ For Fixture/Luminaire Support of 50 lbs or less
- ▶*For Fixture/Luminaire Support of 90 lbs or less, Fan Support of 70 lbs or less

See Page A5 for Covers & Rings


Cat. No.	Depth	Knockouts		Cu. Inch	Std. Pkg.
		Sides 1, 3, 5, 7	Sides 2, 4, 6, 8		
2CB	2"	1 - 1/2"	1 - 3/4"	24.4	25
25CB	2-1/2"	1 - 1/2"	1 - 3/4"	30.5	25
3CB	3"	1 - 1/2"	1 - 3/4"	37.0	25
3CB-75/100	3"	1 - 3/4"	1 - 1"	37.0	25
35CB	3-1/2"	2 - 1/2"	2 - 3/4"	43.0	25
35CB-75/100	3-1/2"	1 - 3/4"	1 - 1"	43.0	25
4CB	4"	2 - 1/2"	2 - 3/4"	49.2	25
4CB-75/100	4"	2 - 3/4"	2 - 1"	49.2	25
*4CB-F	4"	Side 1, 5; 1 - 1/2" Side 3, 7; 2 - 1/2"	Side 2, 6; 1 - 3/4" Side 4, 8; 2 - 3/4"	49.2	25
5CB	5"	2 - 1/2"	2 - 3/4"	61.7	10
6CB	6"	2 - 1/2"	2 - 3/4"	73.5	10




2CB
25CB
3CB




35CB
4CB
5CB
6CB



3CB-75/100
35CB-75/100




4CB-75/100



FAN-RATED CONCRETE BOX


Inside tabs for fans up to 70 lbs (dynamic)




*4CB-F

4" OCTAGONAL CONCRETE BOX COVERS


Cat. No.	Description	Std. Pkg.
CB-B	Flat, Blank	25
CB-B-PT	Flat, Blank - With 12" #12AWG Solid Pigtail	25
CB-BK	Flat With 3 - 1/2" KO's & 2 - 3/4" KO's	25
CB-BK-STUD	2 - 1/2" KO's & 2 - 3/4" KO's - With #3/8-18 Threaded Fixture Stud	25




CB-B



CB-B-PT



CB-BK



CB-BK-STUD