



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



50MR16TFL35C(EXN 50W 12V Hal MR16 GU5.3 Bi-Pin Base Reflector Cover *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | 50MR16TFL35C(EXN |
| Manufacturer | Sylvania-Ledvance |
| Description | Tungsten Halogen Tru Aim MR16 Titan Axial Filament Uv Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50WATT 12VOLT Flood Beam |
| Weight per unit | 0.0900 (lbs/each) |
| Product Category | Halogen Reflector Ar, BR, JDR, |

Features

| | |
|----------------|-------------|
| average life | 4000 |
| Base | GU5.3 Bipin |
| beam angle | 36 |
| dimnable | Yes |
| Lamp Type | MR16 |
| lumens | 900 |
| Shape | MR16 |
| start type | Instant |
| Voltage | 12.00 V |
| Voltage Rating | 12 |
| Wattage | 50 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| color rendering index (cri) | 100 |
| color temperature | 3000 |

Descriptions

| | |
|------------------------|---|
| Description | 50W 12V HAL MR16 GU5.3 BI-PIN BASE REFLECTOR COVER |
| extra long description | SYL 50MR16TFL35CEXN-12V/58309 50MR1 |
| Long Description | Tungsten Halogen Tru Aim MR16 TITAN Axial Filament UV Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50Watt 12Volt Flood Beam |
| Product Type | 50MR16TFL35CEXN 12V 20/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135583094 |
| Manufacturers Part Number | 50MR16/T/FL35/C(EXN)-12V/58309 |
| UPC | 046135583094 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description QUARTZ

Type HALOGEN

Packaging

Carton 1

Package 20

Weight Per each 0.09

Uses, Certifications, and Standards

Application Medium Screwbase or bi-pin

standard EXN