


PART NUMBER	SIZE	"R"	"O"	"H"	"S" MIN	"B" MIN	"L"
5133949	¾"	36"	36"	36"	1 ½"	N/A	56 ½"
5133852	1"	36"	36"	36"	1 ⅞"	N/A	56 ½"
5133884	1 ¼"	36"	36"	36"	2"	N/A	56 ½"
5133866	1 ½"	36"	36"	36"	2"	N/A	56 ½"
5133848	2"	36"	36"	36"	2"	N/A	56 ½"
5133857	2 ½"	36"	36"	36"	3"	N/A	56 ½"
5133820	3"	36"	36"	36"	3 ⅛"	N/A	56 ½"
5133818	3 ½"	36"	36"	36"	3 ¼"	N/A	56 ½"
5133821	4"	36"	36"	36"	3 ⅜"	N/A	56 ½"
5133841	5"	36"	36"	36"	3 ⅝"	N/A	56 ½"
5133877	6"	36"	36"	36"	3 ¾"	N/A	56 ½"



ETL LISTED
 CONFORMS TO UL651
 ETL CONTROL #3107144
 CONFORMS TO NEMA TC3
 SEE NEC ARTICLE 352 FOR USE
 MATERIAL IS RIGID PVC
 BEND TOLERANCE IS ±2°



CANTEX
 INC.
 Fort Worth, TEXAS


90° Elbows Plain End
 Schedule 40 36" Radius Elbows

Drawn By: CD Branch

Date: 10/15/07

Ref.

PART NUMBER	SIZE	"R"	"O"	"H"	"S" MIN	"B" MIN	"L"
5133949	¾"	36"	36"	36"	1 ½"	N/A	56 ½"
5133852	1"	36"	36"	36"	1 ⅞"	N/A	56 ½"
5133884	1 ¼"	36"	36"	36"	2"	N/A	56 ½"
5133866	1 ½"	36"	36"	36"	2"	N/A	56 ½"
5133848	2"	36"	36"	36"	2"	N/A	56 ½"
5133857	2 ½"	36"	36"	36"	3"	N/A	56 ½"
5133820	3"	36"	36"	36"	3 ⅛"	N/A	56 ½"
5133818	3 ½"	36"	36"	36"	3 ¼"	N/A	56 ½"
5133821	4"	36"	36"	36"	3 ⅜"	N/A	56 ½"
5133841	5"	36"	36"	36"	3 ⅝"	N/A	56 ½"
5133877	6"	36"	36"	36"	3 ¾"	N/A	56 ½"



ETL LISTED
CONFORMS TO UL651
ETL CONTROL #3107144
CONFORMS TO NEMA TC3
SEE NEC ARTICLE 352 FOR USE
MATERIAL IS RIGID PVC
BEND TOLERANCE IS ±2°



CANTEX
INC.
Fort Worth, TEXAS

90° Elbows Plain End
Schedule 40 36" Radius Elbows

Drawn By: CD Branch

Date: 10/15/07

Ref.