



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



52511 SGL Recp 15A 125V S-Wire Iv

Pass & Seymour/Legrand

Catalog Number	52511
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Spec Grade Single Receptacle Side, Wire 15A 125V
Weight per unit	0.1606 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Wire Ground
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	SGL RECP 15A 125V S-WIRE IV
extra long description	P&S 52511 RECP SGL 15A 125V S-WIRE
Features	Heavy Duty Steel Mounting Strap
Long Description	Heavy-Duty Spec Grade Single Receptacle Side, Wire 15A 125V
Product Type	Recp SGL 15A 125V S-Wire Iv
Special Features	Auto ground clip, back & side wire, zinc steel strap

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007525113
Manufacturers Part Number	5251-I
UPC	785007525113

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.1606

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting	WALL
nema rating	5-15R
Operating Temperature	-40°-60°C
standard	CULUS, UL 498