



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5266SSAN Straight Blade Angle Plug 3W 15A 125V

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 5266SSAN |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Plug 2POLE 3WIRE 15AMP 125VOLT Angle |
| Weight per unit | 0.8400 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 15 |
| connection | Wire Grounding |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 4 |

Dimensions and Weight

| | |
|------|--------|
| Size | 2.8 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | STRAIGHT BLADE ANGLE PLUG 3W 15A 125V |
| extra long description | P&S PS5266SSAN STR BLD ANGLE PLUG 3 |
| Long Description | Straight Blade Plug 2pole 3wire 15amp 125volt Angle |
| Product Type | STR BLD Angle Plug 3W 15A 125V |
| Special Features | Tri-drive assembly & cord grip screws are standard on all |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007236873 |
| Manufacturers Part Number | PS5266SSAN |
| UPC | 785007236873 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Power Outlet Angle Plug |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 20 |
| Weight Per each | 0.84 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Extra Hard Use |
| nema rating | 5-15P |
| standard | FEDSPEC, CULUS, UL 498 |