



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5276BK Straight Blade Plug 3W 15A 125V Dead Front *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | 5276BK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black, Nylon Material, 1.530 In Diameter, 1.8 In Length, Impact Resistant, Chemical Resistant, 0.1 LB |
| Weight per unit | 0.1004 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 15 |
| connection | Wire Grounding |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 1.8 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | STRAIGHT BLADE PLUG 3W 15A 125V DEAD FRONT |
| extra long description | P&S 5276BK STR BLD PLUG 3W 15A 125V |
| Special Features | Ready to wire from factory with external cord grips |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007527612 |
| Manufacturers Part Number | 5276BK |
| UPC | 785007527612 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Straight Blade |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.1004 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

CULUS, UL 498
