



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5362GRY Recp Dup 20A 125V S+B Wire Gry

*Pass & Seymour/Legrand*

Catalog Number	5362GRY
Manufacturer	Pass & Seymour/Legrand
Description	Ehard Use Spec Grade Duplex Receptacle Back and Side Wire 20A 125V Yellow
Weight per unit	0.2411 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Color	Gray
Finish	Matte

### Dimensions and Weight

Height	3.281
Width	.780



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RECP DUP 20A 125V S+B WIRE GRY
extra long description	P&S 5362GRY RECP DUP 20A 125V S+B W
Long Description	eHard Use Spec Grade Duplex Receptacle Back and Side Wire 20A 125V Yellow
Product Type	Recp Dup 20A 125V S+B Wire Gry
Special Features	Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. 8 hole internal screw-pressure-plate back wire terminals accept #14 – #10 AWG solid or stranded copper or copper-clad conductors. Terminal compartments isolated from each other for posi

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007536218
Manufacturers Part Number	5362GRY
UPC	785007536218

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	10
Package	100
Weight Per each	0.2411

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C