



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 54140 #4 Weld Lug

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | 54140   |
| Manufacturer     | Abb Installation Products, Inc  |
| Description      | Standard Barrel Single Hole Compression Lug, #4 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Gray (Die Color) Insulation Color, 1.42 In Overall Length, Tongue Terminal, 35 KV, 0.02 LB/Ea |
| Weight per unit  | 0.0190 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                 |        |
|-----------------|--------|
| Cable Size      | 4 AWG  |
| insulation      | None   |
| Material        | Copper |
| Number of Holes | 1      |
| Stud Size       | 3/8 in |
| Voltage Rating  | 35 kV  |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | #4 WELD LUG                         |
| extra long description | ABB 54140 No4 CU LUG STD BRL 1HL 3/ |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | COLOR-KEYED    |
| GTIN  | 00786210541402 |
| UPC   | 786210541402   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Standard Barrel                   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 50    |
| Weight Per each | 0.019 |

### Uses, Certifications, and Standards

|          |                     |
|----------|---------------------|
| standard | UL E9809 / UL E9809 |
|----------|---------------------|