

Project Name

Location

Prepared By



NUVO 62-1801R1

7" LED DISK LIGHT WHITE FINISH

Notes

[www] 09-14-2023 23:00:12

General

Status	Future Item
Finish	White
Wattage	11.3W
Style	Contemporary
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Width (in.)	7.4
Height (in.)	1.44

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
CRI	90
Lumen Output	930L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	0.63
Sloped Ceiling	Yes
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Disk Light
Operating Temperature	-20C (-4F) to +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Wet
ENERGY STAR	Yes
ES Unique ID	ESID-4005951
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

Additional Information

Warranty	5-Years
----------	---------

Project Name

Location

Prepared By



Notes

[www] 09-14-2023 23:00:12

General

Status	Future Item
Finish	White
Wattage	11.3W
Style	Contemporary
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Width (in.)	7.4
Height (in.)	1.44

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
CRI	90
Lumen Output	930L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	0.63
Sloped Ceiling	Yes
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Disk Light
Operating Temperature	-20C (-4F) to +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Wet
ENERGY STAR	Yes
ES Unique ID	ESID-4005951
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

Additional Information

Warranty	5-Years
----------	---------