



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5500 Wheeler Avenue
72901-0000, AR Fort Smith
Phone: 479-648-1902
Fax: 479-648-1960



62MAX IP54 Ir Thermometer

Fluke Electronics

Catalog Number	62MAX
Manufacturer	Fluke Electronics
Description	The Fluke 62 Max Infrared Thermometers Are Everything You'D Expect From The Experts In Measuring Temperature In Transformers, Motors, Pumps, Panels, Breakers, Compressors, Duct, Steam Lines, Valves, and Vents In Hard to Reach Areas For Repair and Maintenance. Small In Size, Extremely Accurate and Yet Easy to Use . IP54 Rated For Dust and Water Resistance. Precise Yet Rugged Enough to Take A 3-Meter Drop.
Weight per unit	1.3 (lbs/each)
Product Category	Meters, Panel Instruments

Features

Response Time	500m
Temperature Range	-30 ?°C to 500 ?°C (-22 ?°F to 932 ?°F)

Descriptions

Description	IP54 IR THERMOMETER
extra long description	FLK FLUKE-62-MAX IP54 IR THRMTR
Long Description	The Fluke 62 MAX infrared thermometers are everything you'd expect from the experts in measuring temperature in transformers, motors, pumps, panels, breakers, compressors, duct, steam lines, valves, and vents in hard to reach areas for repair and maintenance. Small in size, extremely accurate and yet easy to use . IP54 rated for dust and water resistance. Precise yet rugged enough to take a 3-meter drop.
Product Type	IP54 Ir THRMTR

Manufacturer Information

Brand	FLUKE
GTIN	00095969620208
Manufacturers Part Number	FLUKE-62 MAX
UPC	095969620208

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
----------------------	---

Packaging

Carton	3
Weight Per each	1.28