

# Door Bells


## Low Voltage

### 600 Series

Edwards 600 Series patented piano-action design requires only the slightest touch. This slim design can be easily installed in minutes. They feature plastic, rust-proof cases and are available in illuminated and non-illuminated models.

#### Features and Specifications

- Surface mounted
- Piano type action
- Plastic case - rust proof
- Normally open momentary contacts



#### Ordering Information

Description	Cat. No.	Maximum Switching Voltage	Color	
			Housing	Center
Illuminated	630L	16V AC	Brown	White
	632L	16V AC	Chrome	Ivory
Non-illuminated	630	48V AC	Brown	White
	631	48V AC	Ivory	White
	634	48V AC	Brown	White
	635	48V AC	Ivory	Black
	636	48V AC	Ivory	White

#### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions		
			Width (in.)	Height (in.)	Depth (in.)
630L	0.04	0.06	7/8	2 7/8	2 5/8
632L	0.02	0.04	7/8	2 7/8	2 5/8
630	0.04	0.06	7/8	2 7/8	2 5/8
631	0.04	0.06	7/8	2 7/8	2 5/8
634	0.05	0.08	3/4	2 5/8	3/4
635	0.05	0.08	3/4	2 5/8	3/4
636	0.05	0.08	3/4	2 5/8	3/4



# Door Bells


## Low Voltage

### 600 Series

Edwards 600 Series patented piano-action design requires only the slightest touch. This slim design can be easily installed in minutes. They feature plastic, rust-proof cases and are available in illuminated and non-illuminated models.

#### Features and Specifications

- Surface mounted
- Piano type action
- Plastic case - rust proof
- Normally open momentary contacts



#### Ordering Information

Description	Cat. No.	Maximum Switching Voltage	Color	
			Housing	Center
Illuminated	630L	16V AC	Brown	White
	632L	16V AC	Chrome	Ivory
Non-illuminated	630	48V AC	Brown	White
	631	48V AC	Ivory	White
	634	48V AC	Brown	White
	635	48V AC	Ivory	Black
	636	48V AC	Ivory	White

#### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions		
			Width (in.)	Height (in.)	Depth (in.)
630L	0.04	0.06	7/8	2 7/8	2 5/8
632L	0.02	0.04	7/8	2 7/8	2 5/8
630	0.04	0.06	7/8	2 7/8	2 5/8
631	0.04	0.06	7/8	2 7/8	2 5/8
634	0.05	0.08	3/4	2 5/8	3/4
635	0.05	0.08	3/4	2 5/8	3/4
636	0.05	0.08	3/4	2 5/8	3/4

