

Project Name

Location

Prepared By



NUVO 65-1082

4FT LED CEILING WRAP

Notes

[www] 01-20-2023 09:30:47

General

| | |
|---------------------------|---------------|
| Status | Transitioning |
| Substitute | 65-1211 |
| Fixture Type | Ceiling Wrap |
| Finish | White |
| Wattage | 40W |
| Lumen Output | 3200L |
| CCT (Kelvin) | 4000K |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|-----------------------|----------------------------|
| Technology | LED |
| Color Temperature | Cool White |
| CRI | 90 |
| Voltage | 100V-277V |
| Rated Hours | 50000 |
| Operating Temperature | -20C (-4F) to +45C (+113F) |
| Dimmable | Non-Dimmable |
| Weight (lb.) | 4.47 |
| Material | Steel |

Dimensions

| | |
|--------------|------|
| Height (in.) | 2.63 |
| Width (in.) | 5.5 |
| Length (in.) | 47.5 |

Compliance

| | |
|----------------------|---|
| Safety Listing | cETLus - Listed |
| Location Rating | Damp |
| Energy Star | No |
| DLC Approved | No |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| NEC Compliance | Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5) |
| FCC Compliant | Yes |
| SDS Sheet | LED_Fixture |

Additional Information

| | |
|----------|---------------------------|
| Warranty | 5 Year Limited - Fixtures |
|----------|---------------------------|

Project Name

Location

Prepared By



NUVO 65-1082

4FT LED CEILING WRAP

Notes

[www] 01-20-2023 09:30:47

General

| | |
|---------------------------|---------------|
| Status | Transitioning |
| Substitute | 65-1211 |
| Fixture Type | Ceiling Wrap |
| Finish | White |
| Wattage | 40W |
| Lumen Output | 3200L |
| CCT (Kelvin) | 4000K |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|-----------------------|----------------------------|
| Technology | LED |
| Color Temperature | Cool White |
| CRI | 90 |
| Voltage | 100V-277V |
| Rated Hours | 50000 |
| Operating Temperature | -20C (-4F) to +45C (+113F) |
| Dimmable | Non-Dimmable |
| Weight (lb.) | 4.47 |
| Material | Steel |

Dimensions

| | |
|--------------|------|
| Height (in.) | 2.63 |
| Width (in.) | 5.5 |
| Length (in.) | 47.5 |

Compliance

| | |
|----------------------|---|
| Safety Listing | cETLus - Listed |
| Location Rating | Damp |
| Energy Star | No |
| DLC Approved | No |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| NEC Compliance | Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5) |
| FCC Compliant | Yes |
| SDS Sheet | LED_Fixture |

Additional Information

| | |
|----------|---------------------------|
| Warranty | 5 Year Limited - Fixtures |
|----------|---------------------------|