

Project Name

Location

Prepared By



NUVO 65-656

40W LED SMALL WALL PACK

Notes

(www) 18-27-2023 05:20:07

General

Status	Active
Fixture Type	Wall Pack
Finish	Bronze
Wattage	40W
Lumen Output	4200L-5000L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	70+
Voltage	120V-277V
Beam Angle	80
Rated Hours	50000
Operating Temperature	-40C (-40F) to +45C (+113F)
Dimmable	Non-Dimmable
Photocell or Sensor	Yes - Bypassable
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	5.08
Material	Aluminum / Polycarbonate (PC)

Dimensions

Height (in.)	8.44
Width (in.)	8.5
Extension (in.)	7.45

Compliance

Safety Listing	cULus - Certified
Location Rating	Wet
ENERGY STAR	No
DLC Approved	No
ADA Compliant	No
B.U.G. Rating	B2-U3-G2
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class A
Flicker Free	Yes
SDS Sheet	LED_Fixture

Additional Information

Additional Information	IK10 Lens
Warranty	5-Years