

Project Name

Location

Prepared By



## NUVO 65-719

LED 2 BULLET HEAD SECURITY LGT

### Notes

(revised) 10-27-2023 05:20:07

### General

|                           |                   |
|---------------------------|-------------------|
| Status                    | Active            |
| Fixture Type              | Security Lighting |
| Finish                    | Bronze            |
| Wattage                   | 20W               |
| Lumen Output              | 1900L             |
| CCT (Kelvin)              | 4000K             |
| Temperature               | Cool White        |
| IP Rating                 | IP65              |
| Indoor or Outdoor Fixture | Outdoor           |

### Specifications

|                       |                                 |
|-----------------------|---------------------------------|
| Technology            | LED                             |
| CRI                   | 80+                             |
| Voltage               | 120V                            |
| Beam Angle            | 50                              |
| Rated Hours           | 50000                           |
| Operating Temperature | -30C (-22F) to +50C (+122F)     |
| Dimmable              | Non-Dimmable                    |
| Photocell or Sensor   | Has Photocell                   |
| Lens Material         | Glass                           |
| Surge Protection      | Built-in surge protection - 2KV |
| Weight (lb.)          | 2.66                            |
| Material              | Die-Cast Aluminum               |

### Dimensions

|                 |      |
|-----------------|------|
| Height (in.)    | 6.42 |
| Width (in.)     | 8.16 |
| Extension (in.) | 8.8  |

### Compliance

|                            |                               |
|----------------------------|-------------------------------|
| Safety Listing             | cETLus - Listed               |
| Location Rating            | Wet                           |
| ENERGY STAR                | No                            |
| DLC Approved               | No                            |
| ADA Compliant              | No                            |
| California Status          | Lawful for sale in California |
| Title 20 / 24 Status       | Lawful for sale               |
| California Prop 65         | Lead                          |
| RoHS Compliant             | Yes                           |
| FCC Compliant              | Yes                           |
| Canadian Standard ICES-005 | Class A                       |
| SDS Sheet                  | LED_Fixture                   |

### Additional Information

|                    |                                       |
|--------------------|---------------------------------------|
| Specification Note | Adjustable Angle from 0 to 90 degrees |
| Warranty           | 5-Years                               |