



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



659 4" STL Conn Concrete Tight

Crouse-Hinds

Catalog Number	659
Manufacturer	Crouse-Hinds
Description	Emt Compression Connector, 4 In Trade Size, Straight Connection Orientation, Zinc Plated, Non-Insulated, 4.08 In Length, 5 In Diameter, 0.87 In Thread Length, 2.45 LB/Ea
Weight per unit	2.5 (lbs/each)
Product Category	Steel Uninsulated Straight Com

Features

dimensions	5.8000 IN X 4.3000 IN X 6.5000 IN
------------	-----------------------------------

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	4 in
------	------

Descriptions

Description	4" STL CONN CONCRETE TIGHT
extra long description	MIDWEST 659 4 EMT CMP CONN
Features	Crouse-Hinds series EMT connectors and couplings are used to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. Our EMT fittings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in steel and zinc die cast. Crouse-Hinds series EMT connectors and couplings are also available painted in seven different colors to better match architectural specifications and preferences.

Manufacturer Information

Brand	Eaton
GTIN	00784564106599
UPC	784564106599

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Compression Connector

Packaging

Carton	1
Package	4
Weight Per each	2.45

Uses, Certifications, and Standards

standard	UL, cUL
----------	---------