



## TRADEMASTER GROUNDING TOGGLE SWITCH

660BKG | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single Pole Switch, Grounded Terminals, 15 amps, 120 volts, Black.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 1  
Special Features: Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
cULus: Yes  
cUL Standard: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.090"  
Height (US): 3.281"  
Width (US): 1.25"

## TECHNICAL INFORMATION

Amps: 15A  
Volts: 120VAC  
Volts (AC): 120

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Trade Agreement Act Compliant





## TRADEMASTER GROUNDING TOGGLE SWITCH

660BKG | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single Pole Switch, Grounded Terminals, 15 amps, 120 volts, Black.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 1  
Special Features: Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
cULus: Yes  
cUL Standard: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.090"  
Height (US): 3.281"  
Width (US): 1.25"

## TECHNICAL INFORMATION

Amps: 15A  
Volts: 120VAC  
Volts (AC): 120

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Trade Agreement Act Compliant

