

---

## TRADEMASTER GROUNDING TOGGLE SWITCH, IVORY

660IG | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Single Pole Switch in ivory, with grounded terminals, is made of a thermoplastic toggle and frame. It has a smooth, quiet toggle action. It is made with high-impact resistant construction. 15 amps, 120 volts.

\*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660IGU

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 1  
Special Features: Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
cULus: Yes  
cUL Standard: Yes  
UL Listing No: UL20  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.090"  
Height (US): 3.281"

Width (US): 1.25"

**TECHNICAL INFORMATION**

Amps: 15A

Volts: 120VAC

Volts (AC): 120

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant