Pass and Seymour
Trademaster® Grounding Toggle Switch, White
Part No. 664WG



Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Brown.

Features & Benefits

Side wire #12 and #14 AWG. Push wire #14 AWG.

Tri-drive ground, terminal, and mounting screws.

Easy-access green hex head ground screw.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007664027
Country Of Origin	Mexico	Material	Thermoplastic
Features	Extra Long Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

Additional Information

Product Environmental Profile	Yes

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Side Only
Number of Gangs	1	Amperage	15 A
Number of Poles	4-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Push Wire	Voltage	120.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		