



68547

F96T8 TL841/HO/PLUS/ALTO/TSC(PKX25)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Recessed Double Contact (R17d)

Coating: Copolymer

Color Temperature: 4100 K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 7625

Package Weight: 27.80 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 86.0 W

Average Life Hours: 30000

Bulb: T8

Color: TL841

CRI: 85

Initial Lumens: 8200

Length: 96.00 IN

Package (LxWxH): 96.25 IN x 6.60 IN x 6.50 IN

Pack By: 25

Special Features: Shatter-Resistant

UPC: 726585685479

ULEPH,ROHS,NSF Splash Zone



68547

F96T8 TL841/HO/PLUS/ALTO/TSC(PKX25)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Recessed Double Contact (R17d)

Coating: Copolymer

Color Temperature: 4100 K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 7625

Package Weight: 27.80 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 86.0 W

Average Life Hours: 30000

Bulb: T8

Color: TL841

CRI: 85

Initial Lumens: 8200

Length: 96.00 IN

Package (LxWxH): 96.25 IN x 6.60 IN x 6.50 IN

Pack By: 25

Special Features: Shatter-Resistant

UPC: 726585685479

ULEPH,ROHS,NSF Splash Zone