



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 693 Combo 2 Switches 3W 15A 120/277V BN

*Pass & Seymour/Legrand*

Catalog Number	693
Manufacturer	Pass & Seymour/Legrand
Description	15 Amps 120/277 Volts, Double Three-Way Combination Switch, Non-Grounding, Brown.
Weight per unit	0.2500 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	Side wire, non-grounding
Contact Configuration	N-O
Contact Rating	15 Amp, 120/277 VAC
operating cycles	30000
Poles	3-way
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2 SWITCHES 3W 15A 120/277V BN
extra long description	P&S 693 COMBO 2SWITCHES 3WAY 15A120
Long Description	15 amps 120/277 volts, Double Three-way Combination Switch, Non-Grounding, Brown.
Product Type	Combo 2SWITCHES 3WAY 15A120/277V BN
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007693003
UPC	785007693003

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Non-Grounding Combination Two Three-Way Switches



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	UL20