



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 696IG Combo 2SW 1P+3W 15A 120/277V Iv

*Pass & Seymour/Legrand*

Catalog Number	696IG
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, 3-Way Double Combination Switch, 15A 120/277V, Ivory.
Weight per unit	0.2400 (lbs/each)
Product Category	Combination Devices

### Features

action	(1) SP & (1) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30k.0
Poles	1 & 3-Way
Voltage	120.0 V
Voltage Rating	0.433212996389892
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	Ivory
Finish	Matte

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2SW 1P+3W 15A 120/277V IV
extra long description	P&S 696IG COMBO 2SW 1P+3W 15A 120/2
Features	Combination
Long Description	Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory.
Product Type	Combo 2SW 1P+3W 15A 120/277V I
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006216
Manufacturers Part Number	696-IG
UPC	785007006216

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Package	50
Weight Per each	0.24

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20