



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 696LA Combo 2SW 1P+3W 15A 120/277V La *Pass & Seymour/Legrand*

Catalog Number	696LA
Manufacturer	Pass & Seymour/Legrand
Description	15 Amps, 120/277 Volts, Single Pole, Three-Way Combination Switch, Non-Grounding, Light Almond.
Weight per unit	0.2300 (lbs/each)
Product Category	Wiring Devices

### Features

action	(1) SP & (1) 3W
actuator	Toggle
amperage rating	15
connection	Side wire, non-grounding
Contact Configuration	N-O
Contact Rating	15 Amp, 120/277 VAC
operating cycles	30000
Poles	1 & 3-Way
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2SW 1P+3W 15A 120/277V LA
extra long description	P&S 696-LA COMBO 2 SW 1P+3W 15A 120
Long Description	15 amps, 120/277 volts, Single Pole, Three-way Combination Switch, Non-Grounding, Light Almond.
Product Type	Combo 2 SW 1P+3W 15A 120/277V La
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007690262
Manufacturers Part Number	696LA
UPC	785007690262

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Non-Grounding Combination Single Pole & Three-Way Switches



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.23

## Uses, Certifications, and Standards

Application ..... Residential/Commercial

environmental conditions ..... Flammability: UL94 V2

Mounting ..... WALL

Operating Temperature ..... Maximum continuous +60°C, minimum -30°C

standard ..... UL20