



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6RLAG206LM30K90C 6" 11W Led Gimbal 30K 600LM 120V 90cri *Lithonia Lighting*

Catalog Number	6RLAG206LM30K90C
Manufacturer	Lithonia Lighting
Description	The 6RLA Adjustable Replaces 65 Watt Incandescent Lamp, Producing Over 650 Lumens. This Luminaire Is Designed For Vertical Aiming Up to 35 Degrees and 359 Degrees Rotation.
Weight per unit	3.9 (lbs/each)
Product Category	Lighting Accessories

Features

average life	50,000
Lamp Type	LED - Static
lumens	600 LM
Maximum Operating Temperature	25
media	Yes
Power Source	Plug-In
Shape	Round
Voltage Rating	120
Wattage	10.5

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000
Lens Color	WHITE
Lens Material	Polycarbonate

Descriptions

Construction	Retrofit
Description	6" 11W LED GIMBAL 30K 600LM 120V 90CRI
extra long description	LITH 6RLA G2 06LM 30K 90CRI WFL 120
Long Description	The 6RLA Adjustable replaces 65 watt incandescent lamp, producing over 650 lumens. This luminaire is designed for vertical aiming up to 35 degrees and 359 degrees rotation.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00661209652669
Manufacturers Part Number	6RLA G2 06LM 30K 90CRI WFL 120
UPC	661209652669



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED ARCHITECTURAL & SPECIFICATION LIGHTING

Trade Size

aperture size 6 in

Packaging

Carton 1

Weight 3.358

Weight Per each 3.9

Uses, Certifications, and Standards

Application Healthcare,Residential,Retrofit

environmental conditions Indoor