



Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID 71A8251001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information		Input Frequency	
ANSI Code	S50	Input Frequency	60 Hz
Lamp Type	250W HPS	Input Current (Open Circuit)	1.82/1.1/0.92/0.83/0.45 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.32/0.82/0.66/0.56/0.32 A
Circuit Type	CWA	Input Current (Short Circuit)	0.81-1.22/0.44-0.66/0.39-0.58/0.32-0.49/0.2-0.3 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	3.69-4.51 A
Base Model	71A8251	Constant Wattage Deviation	Within Trapezoid
Core Size	4 x 4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI501-H4	Open Circuit Voltage	188 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	2.66/1.54/1.32/1.16/0.66 A A
Capacitor Value	35 MFD	Input Power (Nom)	300 W
Capacitor Catalog Number	7C350P24RA	Rated Lamp Power	250 W
Capacitor Requirements	240V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.65 in	Wire Length by Color	12"
Capacitor Height	3.7 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring	2'
Input Voltage	120/208/240/277/480 V	Recommended Fuse Value	7/4/4/3/2 A

Core & Coil (71A) HPS 200W - 400W

Approval and Application

Open Circuit Voltage Test (Volts)	169-207 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data

Order product name	CORE & COIL HID 71A8251001D
EAN/UPC - Product	781087114193
Order code	913710414701
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710414701
Net Weight (Piece)	5.612 kg

Dimensional drawing



HPS BAL 250W S50 5-TAP KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A8251001D	3.6 in	2 in	4.8 in	4.4 in	4.3 in	3.9 in

