



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7200ST 2 In Emt Comp Conn Insul Steel

*Appleton/Oz Gedney*

Catalog Number	7200ST
Manufacturer	Appleton/Oz Gedney
Description	Features:2 1/4IN Dia X 2 11/16IN Length, 11/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:2IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	1.0 (lbs/each)
Product Category	Steel Insulated Straight Compr

### Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Insulated Throat
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	2
------	---

### Descriptions

Description	2 IN EMT COMP CONN INSUL STEEL
extra long description	EGS 7200ST 2 IN EMT COMP CONN INSUL
Long Description	Features:2 1/4IN Dia X 2 11/16IN Length, 11/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:2IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	2 In Emt Comp Conn Insul Steel
Special Features	2 1/4 IN Dia X 2 11/16 IN Length, 11/16 IN Thread Length, Concretetight

### Manufacturer Information

Brand	Appleton/Oz Gedney
Manufacturers Part Number	7200ST

### Taxonomies, Classifications, and Categories

Type	EMT Conduit Straight Compression Connector
------	--------------------------------------------

### Trade Size

Trade Size	2
------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1

## Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1
Temperature Rating	90