

# Specifications



Photo is representative

## Eaton 726016-12FD

Eaton B-Line series ground mounted panel enclosure, 72" height, 16" length, 60" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket

### General specifications

<b>PRODUCT NAME</b>	Eaton B-Line series type 12 panel enclosures
<b>CATALOG NUMBER</b>	726016-12FD
<b>UPC</b>	782051408102
<b>PRODUCT LENGTH/DEPTH</b>	16 in
<b>PRODUCT HEIGHT</b>	72 in
<b>PRODUCT WIDTH</b>	60 in
<b>PRODUCT WEIGHT</b>	477.7 lb
<b>CERTIFICATIONS</b>	UL 508A CSA C22.2. NEMA



### Material/finish

**MATERIAL** Carbon steel

### Model

**STYLE** Large double door

<b>WALL THICKNESS</b>	12 gauge
<b>FINISH COLOR</b>	Painted
<b>COLOR</b>	ANSI 61 gray

<b>MODEL</b>	12FD enclosure
<b>COVER TYPE</b>	Hinged
<b>MOUNTING METHOD</b>	Ground
<b>MOUNTING HOLE DETAILS</b>	Ground mount legs
<b>LOCKING PROVISIONS</b>	Key lock padlock provision
<b>CLOSURE TYPE</b>	Hinged
<b>SPECIAL FEATURES</b>	Plated door clamps

<b>Standards</b>	
<b>NEMA RATING</b>	12
<b>COUNTRY OF ORIGIN</b>	US

<b>Resources</b>	
<b>CATALOGS</b>	<a href="#">Electrical Enclosure Catalog</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - 726016-12FD</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
 All other trademarks are property of their respective owners.



# Specifications



Photo is representative

## Eaton 726016-12FD

Eaton B-Line series ground mounted panel enclosure, 72" height, 16" length, 60" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket

### General specifications

<b>PRODUCT NAME</b>	Eaton B-Line series type 12 panel enclosures
<b>CATALOG NUMBER</b>	726016-12FD
<b>UPC</b>	782051408102
<b>PRODUCT LENGTH/DEPTH</b>	16 in
<b>PRODUCT HEIGHT</b>	72 in
<b>PRODUCT WIDTH</b>	60 in
<b>PRODUCT WEIGHT</b>	477.7 lb
<b>CERTIFICATIONS</b>	UL 508A CSA C22.2. NEMA

**EATON**

*Powering Business Worldwide*

### Material/finish

**MATERIAL**

Carbon steel

### Model

**STYLE**

Large double door

<b>WALL THICKNESS</b>	12 gauge
<b>FINISH COLOR</b>	Painted
<b>COLOR</b>	ANSI 61 gray

<b>MODEL</b>	12FD enclosure
<b>COVER TYPE</b>	Hinged
<b>MOUNTING METHOD</b>	Ground
<b>MOUNTING HOLE DETAILS</b>	Ground mount legs
<b>LOCKING PROVISIONS</b>	Key lock padlock provision
<b>CLOSURE TYPE</b>	Hinged
<b>SPECIAL FEATURES</b>	Plated door clamps

<b>Standards</b>	
<b>NEMA RATING</b>	12
<b>COUNTRY OF ORIGIN</b>	US

<b>Resources</b>	
<b>CATALOGS</b>	<a href="#">Electrical Enclosure Catalog</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - 726016-12FD</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
 All other trademarks are property of their respective owners.

