



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



72C5282NP001 1-70W 120/277 MH Bal *Advance By Signify*

| | |
|------------------|---|
| Catalog Number | 72C5282NP001 |
| Manufacturer | Advance By Signify |
| Description | Versatility In Commercial Applications Low Noise For Indoor Use;Two Dual Voltage Configurations Available: 120V/277V For The U.S Market and 120V/347V For The Canadian Market The Philips Advance Line Of F-Can Hid Ballasts Comes In Two Dual-Voltage Configurations For The Us and Canadian Market. Ballasts For These Luminaires Are Most Often Encased and Potted In Fluorescent Ballast Type Cans. Utilizes UI Class A (90°C) Insulation;Has Built-In, Automatically Resetting, Thermal Protector Which Disconnects The Ba |
| Weight per unit | 8.9 (lbs/each) |
| Product Category | Pulse Start Hid Ballasts |

Features

| | |
|-----------------|--------------|
| amperage rating | 1.25/0.55 |
| ANSI Code | M98/143 |
| Ballast Factor | 1 |
| Circuit Type | HX-HPF |
| Lamp Type | METAL HALIDE |
| Number of Lamps | 1 |
| Power Factor | 0.90 |
| Power Rating | 70 |
| start type | Pulse |
| Voltage Rating | 120/277 |
| Wattage | 70 |
| Wire Length | 12 |
| Wire Type | STRANDED |

Material, Color, and Finish

| | |
|------------------|-------|
| Housing Material | Metal |
|------------------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 1.02 |
| Length | 0.47 |
| Width | 1.54 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 1-70W 120/277 MH BAL |
| extra long description | ADV 494112 MH BAL 70W M98/143 120/2 |
| Long Description | Versatility in commercial applications Low noise for indoor use;Two dual voltage configurations available: 120V/277V for the U.S market and 120V/347V for the Canadian market The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans. Utilizes UL Class A (90°C) insulation;Has built-in, automatically resetting, thermal protector which disconnects the ba |
| Product Type | MH Bal 70W M98/143 120/277V Fcan |
| Special Features | Suitable for Outdoor; UL, CSA, RoHS |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Signify Electronics |
| GTIN | 00781087025253 |
| Manufacturers Part Number | 494112 |
| UPC | 781087025253 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | HID BALLASTS |
| Type | Magnetic HID |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 8.86 |

Uses, Certifications, and Standards

| | |
|------------------|---|
| Frequency Rating | 60 |
| standard | CSA certificate;UL certificate;RoHS Compliant |