



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



74020 Bender Handle, 1" X 44"

Ideal

| | |
|------------------|--|
| Catalog Number | 74020 |
| Manufacturer | Ideal |
| Description | Ideal, Bender Handle, Construction: Rugged Steel, Conduit Size: 1 In Emt, 3/4 In Rigid and 3/4 In Imc, Finish: Enamel, Length: 44 In |
| Weight per unit | 6.0 (lbs/each) |
| Product Category | Hand Tool Bits, Parts, Acessor |

Features

| | |
|--------------|---------------------------------------|
| Conduit Size | 1 IN EMT, 3/4 IN Rigid And 3/4 IN IMC |
|--------------|---------------------------------------|

Descriptions

| | |
|------------------------|--|
| Construction | Rugged Steel |
| Description | BENDER HANDLE, 1" X 44" |
| extra long description | IDEAL 74-020 Bender Handle,Ideal,1. |
| Features | Baked-on blue enamel finish on the bender handle resists corrosion and enhances visibility. |
| Long Description | IDEAL, Bender Handle, Construction: Rugged Steel, Conduit Size: 1 IN EMT, 3/4 IN Rigid And 3/4 IN IMC, Finish: Enamel, Length: 44 IN |
| Product Type | Bender Handle, Ideal, 1.000 In Emt, 3/4 In RGD and 3/4 In Imc C |
| Special Features | Features: Rugged, Steel Construction For Long-Term Durability; Baked-On Blue Enamel Finish Resists Corrosion And Enhances Visibility; Convenient Bending Guide For Offset Bends;Lifetime Warranty; Finish: Enamel; Length: 44 IN |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250740208 |
| Manufacturers Part Number | 74-020 |
| UPC | 783250740208 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------|
| Category Description | HAND TOOLS |
|----------------------|------------|

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 6 |

Uses, Certifications, and Standards

| | |
|-------------|-------------|
| Application | For Hickeys |
| standard | RoHS |