



Powering Business Worldwide

7501-9A

SWITCH DECOR. SP 15A 120/277V AL WH

UPC: 032664737268

Brand Name: Eaton

Sub Brand: ARROW HART

Type: 4-Way

Special Features: Standard Grade, Wiring Type Side and Push Wire, Grounding

Application: Industrial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Connection: Screw

Actuator: Framed Toggle

Color: Light Almond

Contact Configuration: Switches

Size: 1.05 In DepthX 1.31 In WidthX 2.40 Back X 3.28 Length
Screw to Screw

Mounting: Wall

Operating Temperature: -20 To 60 Deg C

7501-9B

SWITCH DECOR. SP 15A 120/277V AG BR

UPC: 032664737275

Brand Name: Cooper Wiring Devices

Type: Single Pole, Grounding, Lighted Switch

Special Features: Lighted, Standard Grade, Wiring Type Side and Push Wire, Grounding

Application: Industrial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Connection: Screw

Actuator: Framed Toggle

Color: Light Almond

7501-9BK

SWITCH DECOR. SP 15A 120/277V AG BK

UPC: 032664737282

Brand Name: Cooper Wiring Devices

Type: 3-Way

Special Features: Standard Grade, Lighted, Wiring Type Side and Push Wire, Grounding

Application: Industrial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Connection: Screw

Actuator: Toggle

Color: Light Almond



Powering Business Worldwide

7501-9GY

SWITCH DECOR. SP 15A 120/277V AG GY

UPC: 032664737299

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 250 Vac
Material: Nylon
Color: Light Almond
NEMA Rating: 6-20R
Mounting: Flush
Connection: Screw
Size: 0.83 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon
Temperature Rating: -20C to 70C (-4F to 158F)

7501-9LA

SWITCH DECOR. SP 15A 120/277V AG LA

UPC: 032664737305

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon
Color: Light Almond
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 0.83 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

7501-9V

SWITCH DECOR. SP 15A 120/277V IV WH

UPC: 032664737312

Brand Name: Cooper Wiring Devices

Type: Screw

Special Features:

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Color: Light Almond

7501-9W

SWITCH DECOR. SP 15A 120/277V AG WH

UPC: 032664737329

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (2) Toggle Switch

Special Features: Wiring Type Back and Side Wire, Color Light Almond

Application: Commercial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Size: 1.37 In Width X 0.88 In Depth

Operating Temperature: -20 To 60 Deg C



Powering Business Worldwide

7501A

Switch Decorator SP 15A 120/277V AL

UPC: 032664627514

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (1) 1 Pole Toggle Switch, (1) 3-Way Toggle Switch

Special Features: Wiring Type Back and Side Wire, Color Light Almond

Application: Commercial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Operating Temperature: -20 To 60 Deg C

7501A-BOX

Switch Decorator SP 15A 120/277V AL

UPC: 032664627743

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (2) 3-Way Toggle Switch

Special Features: Wiring Type Back and Side Wire, Color Light Almond

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 15 Amp

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Operating Temperature: -20 To 60 Deg C



Powering Business Worldwide

7501A-C

Switch Decorator SP 15A 120/277V AL Can

UPC: 032664643422

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (1) Toggle Switch, (1) Pilot Light

Special Features: Wiring Type Back and Side Wire, Color Light Almond, With Red Lexan Pilot Lens, Neon Lamp

Application: Commercial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Wattage: 25 W (Pilot Light)

Number Of Poles: 1

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Size: 1.37 In Width X 0.95 In Depth

Operating Temperature: -20 To 60 Deg C

7501B-BOX

Switch Decorator SP 15A 120/277V BR

UPC: 032664627750

Brand Name: Eaton

Sub Brand: EATON

Type: Duplex, Decorator, Straight Blade

Special Features: Standard Grade, Auto Grounding, Wiring Type Side Wire and Push Wire

Application: Standard grade deco

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Light Almond

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 8.1 X 4.4 X 2 IN

Environmental Conditions: Indoor

Dielectric Strength: 125 Vac

Insulation: Impact Resistant Thermoplastic

Temperature Rating: INDOOR



Powering Business Worldwide

7501BK-BOX

Switch Decorator SP 15A 120/277V BK

UPC: 032664627842

Brand Name: Eaton

Sub Brand: EATON

Type: Duplex, Decorator, Straight Blade

Special Features: Standard Grade, Wiring Type Side Wire and Push Wire

Application: Standard grade deco

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Light Almond

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 8 X 4.25 X 1.93 IN

Environmental Conditions: Indoor

Dielectric Strength: 125 Vac

Insulation: Impact Resistant Thermoplastic

Temperature Rating: INDOOR

7501BK-SP-C

Switch Decorator SP 15A 120/277V BK Can

UPC: 032664643736

Brand Name: Eaton

Sub Brand: ARROW HART

Special Features: Standard Grade, Wiring Type Side and Push Wire, Grounding

Application: Industrial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Number Of Poles: 1

Connection: Screw

Actuator: Framed Toggle

Color: Light Almond

Contact Configuration: Switches

Size: 0.75 In Width X .88 In Depth X 2.13 Back Length X 3.28
Screw to Screw

Mounting: Wall

Operating Temperature: -20 To 60 Deg C



Powering Business Worldwide

7501GY-BOX

Switch Decorator SP 15A 120/277V GY

UPC: 032664627859

Brand Name: Eaton

Sub Brand: ARROW Hart

Type: 3-Way

Special Features: Standard Grade, Wiring Type Side and Push Wire, Grounding

Application: Industrial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Connection: Screw

Actuator: Framed Toggle

Color: Light Almond

Contact Configuration: Switches

Size: 0.75 In Width X .88 In Depth X 2.13 Back Length X 3.28 Screw to Screw

Mounting: Wall

Operating Temperature: -20 To 60 Deg C

7501GY-SP-C

Switch Decorator SP 15A 120/277V GY Can

UPC: 032664643743

Brand Name: Cooper Wiring Devices

Type: Duplex, Straight Blade

Special Features: Standard Grade, Auto Grounding, Wiring Type Side Wire and Push Wire

Application: Residential

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Light Almond

NEMA Rating: 5-15R

Connection: Screw



Powering Business Worldwide

7501LA

Switch Decorator SP 15A 120/277V LA

UPC: 032664627545

Brand Name: Eaton

Sub Brand: EATON

Type: Duplex, Straight Blade

Special Features: Standard Grade, Wiring Type Side Wire and Push Wire

Application: Standard grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Light Almond

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 1.31 In Width X 0.69 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 125 Vac

Insulation: Receptacles

Temperature Rating: '-20C to 60C

7501LA-BOX

Switch Decorator SP 15A 120/277V LA

UPC: 032664627767



Powering Business Worldwide

7501V

Switch Decorator SP 15A 120/277V IV

UPC: 032664627576

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Duplex, Decorator, Straight Blade

Special Features: Wiring Type Back and Side Wire

Application: Commercial grade dec

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: Light Almond

NEMA Rating: 5-20R

Mounting: Flush

Connection: Screw

Size: 1.32 In Width X 0.84 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 2000 V

Insulation: Nylon Face, PVC Base

Temperature Rating: -20C to 70C (-4F to 158F)

7501V-BOX

Switch Decorator SP 15A 120/277V IV

UPC: 032664627774



Powering Business Worldwide

7501V-C

Switch Decorator SP 15A 120/277V IV Can

UPC: 032664643453

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single & Duplex Receptacles

Special Features: Wiring Type Back Wire and Side Wire

Application: Commercial grade dec

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: White

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 0.82X 1.32X 1.98X4.19IN

Environmental Conditions: See Spec Sheet

Dielectric Strength: 2000 V

Insulation: Nylon Face, PVC Base

Temperature Rating: -20C to 70C (-4F to 158F)

7501V-JP;51

7501V Sold in Boxes of 10 Can

UPC: 032664643569



Powering Business Worldwide

7501W

Switch Decorator SP 15A 120/277V WH

UPC: 032664627606

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single & Duplex Receptacles
Special Features: Wiring Type Back Wire and Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: White
NEMA Rating: 5-15R
Mounting: Flush
Connection: Screw
Size: 0.82X 1.32X 1.98X4.19IN
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)

7501W-BOX

Switch Decorator SP 15A 120/277V WH

UPC: 032664627781

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Single, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: Ivory
NEMA Rating: 5-20R
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth



Powering Business Worldwide

7501W-C

Switch Decorator SP 15A 120/277V WH Can

UPC: 032664643460

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: White
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)

7501W-JP;51

7501W Sold in Boxes of 10 Can

UPC: 032664643583

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Duplex, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: Black
NEMA Rating: 5-20R
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth X 4.19 In Height



Powering Business Worldwide

C7501V-SP

Switch Deco SP 15A 120/277V W/Wlplt IV

UPC: 032664644184