

Specifications



Photo is representative



Eaton 7623V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 647383

General specifications

PRODUCT NAME	Eaton commercial grade decorator switch
CATALOG NUMBER	7623V-BOX
UPC	032664647383
PRODUCT LENGTH/DEPTH	4.45 in
PRODUCT HEIGHT	1.88 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.24 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed cULus Listed
PRODUCT TYPE	Commercial grade decorator switch



Powering Business Worldwide

Product specifications

ALLOWABLE WIRE SIZE #14-10 AWG

SPECIAL FEATURES Box

TYPE Switch decorator

AMPERAGE RATING 20A

VOLTAGE RATING 120/277 V

NUMBER OF POLES Three-way

PHASE Single-phase

WIRING METHOD Back and push

SWITCH TYPE Three-way

MOUNTING METHOD Flush

CLOSURE TYPE Maintained

LOAD TYPE INC
Fan
LED
ELV
HAL
FLR
CFL
Motor Control
MLV

MATERIAL Thermoplastic

ACTUATOR Antimicrobial paddle

COLOR Ivory

Resources

[Eaton Specification Sheet - 7623V-BOX](#)

SPECIFICATIONS AND DATASHEETS

[Arrow Hart commercial specification grade AC decorator switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

