



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7842MD 40A 2P SNGL PH Ac Motor Disconnet

*Pass & Seymour/Legrand*

Catalog Number	7842MD
Manufacturer	Pass & Seymour/Legrand
Description	Double-Pole, Single Phase Switch (7842), 40 Amps, 600VS
Weight per unit	0.3100 (lbs/each)
Product Category	Misc Wiring Devices

### Features

actuator	Toggle
amperage rating	40
connection	Side & Back Wired
load	40A
operating cycles	50000
Poles	2
Voltage	600.0 V
Voltage Rating	600
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	Black
Finish	Matte

### Dimensions and Weight

Size	1.753" Depth x 1.8255" Width x 2.375" Height
------	--

### Descriptions

Description	40A 2P SNGL PH AC MOTOR DISCONNENET
extra long description	P&S 7842MD 40A 2P SNGL PH AC MOTOR
Long Description	Double-Pole, Single Phase Switch (7842), 40 Amps, 600Vs
Product Type	40A 2P SNGL PH Ac Motor Disconnet
Special Features	Double Pole, Single Phase Switch, Canada Only Motor Disconnect

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267716
Manufacturers Part Number	7842-MD
UPC	785007267716

### Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

### Trade Size

Amperage	40.0
----------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.31

## Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuos +75°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed